

# Desktop Power Supply Unit



## Features

- IEC/EN/UL 62368-1 & 60950-1
- 100-240 VAC Universal Input, Without Any Slide Switch
- Regulated Output With Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- CEC, DoE Level VI, Energy Star, ErP Stage 2, CoC Tier 2, NRCAN & GEMS Level VI
- No Load Power Consumption Less Than 0.075 W



## Input Specification

Voltage	Universal 100 ... 240 VAC, Single Phase
Frequency	50 ... 60 Hz
Current	1 A max.
Inrush Current	70 A max. / 230 VAC Cold Start @ 25 °C, Full Load
Efficiency	84.25% @ 115 & 230 VAC
Power Consumption	100 mW @ 115 VAC & 230 VAC & No Load
Protection	Internal Primary Current Fuse
Configuration	IEC60320 C8

## Output Specification

Voltage	5 V ± 6%
Current	5 A max.
Regulation	4.7 V min. / 5 V typ. / 5.3 V max.
Ripple & Noise	80 mVp-p max.
Total Power	25 W max.
Load Regulation	± 5% (Typ.)
Transient Response	0.5 ms for 50% Load Change Typ.
Hold-Up Time	10 ms @ Full Load
Configuration	2.5 x 5.5 mm Barrel Plug
DC Cord	16 AWG

## Safety

Insulation Resistance	10 MOhm for 500 VDC (Primary to Secondary)
EMI Requirement	CE Class B, Conduction and Radiation Met
Approvals	CB / UL / cUL / FCC / GS / CE / PSE / BSMI / CCC / RCM / LPS
Over Voltage Protection (OVP)	V out * 180% (max.)
Short Circuit Protection (SCP)	Automatic recovery after short-circuit fault being removed
Over Current Protection (OCP)	I out * 200% (max.)

### Notes

When short circuit protection or over current protection is activated, the power supply will shutdown automatically  
Once the abnormal condition resulting in the failure is removed, the power supply will restart accordingly  
When over voltage protection is activated, the power supply will shutdown

## Electrical

Topology	Switching Flyback
Dielectric Withstand	3 kVAC Primary - Secondary for 1 min.
Leakage Current	0.25 mA @ 2Pin
Efficiency	DoE Level VI, Energy Star, ErP Stage 2, CoC Tier 2, NRCAN & GEMS Level VI Certified
EMC Standards	EN55032 / EN61000-3-2,3 / EN55024
MTBF	300000 Calculated Hours at 25 °C

# Desktop Power Supply Unit




## Operation and Environment Performance


Operating Temperature	0 ... 40 °C
Storage Temperature	-20 ... 80 °C
Operating Humidity	20 ... 80% RH
Storage Humidity	10 ... 90% RH
Cooling	Natural Convection Cooling

## Mechanical Specification

Cable Type	16 AWG, UL2468 Wire
Plug Type	∅ 5.5 * ∅ 2.5 * 9.5 mm
Cable Length	1 m
Case Dimensions (L*W*H)	99 x 50 x 33 mm
Material Flammability	UL94V-0
Weight	170 g, Typical




## Cable & Plug Drawing



# Desktop Power Supply Unit




## Adapter Drawing




# Desktop Power Supply Unit



## Derating Curve



## Static Characteristics



**Art Nr.**  
**RND 320-00093**