

KFMPB 15-10 F laminate trimmer

1550 W

metabo®

Application:

Metal laminate trimmer for welding seam preparation

Execution:

- One-touch controller: patented tool-free milling depth adjustment in 0.1 mm increments; stop points for short adjustment times, which prevent accidental adjustment of cutting depth when working
- Universal milling head with three cemented carbide indexable inserts for all chamfer angles of 0-90°
- Stop roller for guidance on tubes for easy weld seam preparation
- Tool-free adjustable recessed handle for safe and even guiding

Advantage:

- Patented mechanical braking system stops the cutter within 2 seconds after power off
- Precise setting of chamfer angle directly via the guide plates
- Side plates protect the user from chips

Delivery:

3x cemented carbide universal reversible tips, stop roller, TX 15 screwdriver, SW 4 screwdriver with T-handle, SW 10 open-end spanner, additional handle, sheet steel carrying box



Art. no.	71027 413
Brand	METABO
Manufacturer Part Number	601755500
Max. idle speed	12500 rpm
Model	KFMPB 15-10 F
Manufacturer Article Number	601755500
Power input	1550 W
Power output	840 W
Max. chamfer height 45°	10 mm
Max. chamfer width 45°	14 mm
Weight	5.1 kg
Cable length	4 m
With soft start	Yes
With overload protection	Yes
With restart protection	Yes
With electronic feedback	Yes
With dead man function	Yes
Gross Weight	13.179 kg
Product Group	745

EAN

4007430298416