

### Einsatzempfehlung

Material	Stahl N/mm <sup>2</sup>				Rostfreie Stähle		Guss		NE-Metalle			Superleg.		Stahl gehärtet	
Zugfestigkeit	<500	<800	<1200 (<HRC38)	<1600 (<HRC48)	<800	<1200	GG	GGG	Al Knetleg.	Al Si<10%	Cu, Ms	Ti/Ni/Co <900	900-1500	HRC 48-57	HRC 58-63
40 00 860 103 - Vc (m/min)	40	30	10	8	12	8			45		80				
40 00 861 383 - Vc (m/min)	50	37	12	10	15	10	31	31	56	50	100	10	6		
Kühlung	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl	Emulsion/Öl		