

## Han3A RJ45 Cat5 PFT 8p, angled



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 215 1108
Specification	Han3A RJ45 Cat5 PFT 8p, angled
HARTING eCatalogue	<a href="https://b2b.harting.com/09452151108">https://b2b.harting.com/09452151108</a>

### Identification

Category	Connectors
Series	RJ45
Element	Panel feed through
Specification	Angled

### Version

Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Fixing	Screwable in cover plates

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance  
Since 1945

## Material properties

Colour (hood/housing)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	2d50e7aa-ec67-400d-80d7-e815e7cdf940
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene

## Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	72 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059610
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)