



## Datasheet for part number DEMA9P

|                                 |                                                          |
|---------------------------------|----------------------------------------------------------|
| Our Catalog Part Number: DEMA9P |                                                          |
| Brand: Cannon                   | Product Category: D Sub Product Line: D Sub Series: D*MA |

| Product Datasheet               |                                                           |
|---------------------------------|-----------------------------------------------------------|
| General                         | D*M High reliable D-Sub Connectors with crimp termination |
| Wire Gauge Range AWG            | Standard: AWG 20-28. High Density: AWG 22-28              |
| Mating Cycles                   | 200                                                       |
| Contact Arrangement             | 9 contacts size 20                                        |
| Dielectric Withstanding Voltage | 1000 VAC at sea level                                     |
| Current Rating                  | 7.5 A max                                                 |
| Contact Resistance              | 10 milli Ohm max                                          |
| Operating Temperature           | -55°/+125°                                                |
| Salt Spray Test                 | 24 hours                                                  |
| Shell Material                  | steel                                                     |
| Shell Finish                    | Yellow chromate over zinc                                 |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                          |
| Insulator Color                 | black                                                     |
| Gender                          | Pin                                                       |
| Contact Type                    | Crimp                                                     |
| Contact Material                | copper alloy                                              |
| Contact Finish                  | gold over nickel                                          |
| Hardware                        | .162 Through Hole                                         |