

## INSTRUCTIONS SHEET FOR EX **GRP** EMPTY ENCLOSURES

---


### 1. Manufacturer

Raychem RPG Pvt. Ltd.  
CEAT Mahal Annexe 463,  
Dr. Annie Besant Road, Worli  
Mumbai 400 030, INDIA

### 2. Product Description

Raychem RPG Ex Empty Enclosures may be used for fitting ATEX/IECEx approved terminals and components. The Glass Reinforced Polyester Enclosures has been manufactured as per the requirements of EN/IEC 60079-0, EN/IEC 60079-7 & EN/IEC 60079-31 and satisfies requirements of ATEX Directive 2014/34/EU. The enclosures has been developed & manufactured in accordance with EN/IEC 80079-34. The enclosures consist of a Lid and Base screwed together with help of stainless steel captive screws and a sealing system which ensures Ingress Protection rating of IP 66 in accordance with IEC 60529.

### 3. Technical Data

Material:	Glass Reinforced Polyester – Graphite added
Surface Colour (RAL Shade):	RAL 9011
Lid Screws:	SS304 Captive Screws
Sealing/Gasket:	Silicone (Operating temperature: -60°C to + 110°C) Viton (Operating temperature: -30°C to + 110°C)
Mechanical Strength:	Impact Energy > 7 Nm
Flammability:	Self-extinguishing, UL 94 V0
Surface Resistance:	< 10 <sup>9</sup> Ohms
Ingress Protection:	IP 66 in accordance with IEC 60529
Marking:	 II 2 GD Ex eb IIC Gb Ex tb IIIC Db
Certification:	SIRA 18 ATEX 3261U IECEx SIR 18.0070U

### 4. Applicable Standards

IEC/EN 60079-0	Explosive atmospheres – Part 0: Equipment – General requirements
IEC/EN 60079-7	Explosive atmospheres – Part 7: Equipment protection by increased safety “e”
IEC/EN 60079-31	Explosive atmospheres – Part 31: Equipment dust ignition protection by enclosure “t”

*Satisfies requirements of ATEX Directive 2014/34/EU – Equipment for Potentially Explosive atmosphere*

**5. Model Number**

Part Code	Box Size			Bolt Size	Lid Screws Quantity	Tightening Torque (Nm)
	Length (A) (mm)	Width (B) (mm)	Depth (C) (mm)			
GRJ 807555	80	75	55	M4	4	4
GRJ 117555	110	75	55	M4	4	4
GRJ 167555	160	75	55	M4	4	4
GRJ 197555	190	75	55	M4	4	4
GRJ 167575	160	75	75	M4	4	4
GRJ 807575	80	75	75	M4	4	4
GRJ 117575	110	75	75	M4	4	4
GRJ 197575	190	75	75	M4	4	4
GRJ 121290	122	120	90	M6	4	4
GRJ 161690	160	160	90	M6	4	4
GRJ 221290	220	120	90	M6	4	4
GRJ 261690	260	160	90	M6	4	4
GRJ 361690	360	160	90	M6	4	4
GRJ 252512	255	250	120	M6	4	4
GRJ 252516	255	250	160	M6	4	4
GRJ 402512	400	250	120	M6	4	4
GRJ 402516	400	250	160	M6	4	4
GRJ 404012	400	405	120	M6	4	4
GRJ 404020	400	405	201	M6	4	4
GRJ 602512	600	250	120	M6	6	4
GRJ 602516	600	250	160	M6	6	4

**6. Installation & Safety Precautions**

The following points must be noted when assembling final equipment:

1. Only ATEX/IECEx certified terminals and components must be installed in an enclosure.
2. Gasket works as a sealing between the lid and base which provides an Ingress Protection rating of IP 66 in accordance with IEC 60529. The gasket must be undamaged before initial operation. If lid has been opened for occasional inspection, it shall be verified that gasket material has not been adhered to the base of junction Box.
3. Lid and base must be screwed together with help of stainless steel captive screws according to the specified tightening torque.
4. Electrical connections must be performed only by trained electricians & applicable code of practices.
5. The Creepage & Clearance distances must be maintained between bare conductive parts in accordance with applicable code of practices.
6. Entries to the enclosures must be either threaded or plain entries which can be fitted on any side of the enclosure, within the following constraints - a minimum of 5 mm is maintained between the cable entry holes and also: (a) the distance between hole centres of adjacent cable glands/plugs/locknuts will clear it's across corners dimensions and (b) the distance

from the hole centre to the edge of enclosure must be sufficient to clear the across corner dimensions of cable glands/plugs/locknuts.

7. The cable glands must be fitted according to the information provided by cable glands manufacturer. When the temperature is higher than 70 °C at the entry point or 80 °C at the branching point of the conductors, information shall be marked on the equipment exterior to provide guidance to the user on the proper selection of cable and cable gland or conductors. Ensure all unused device openings are fitted with certified blanking elements or stop plug, which shall be removable by aid of a tool.
8. The entry hole shall be sized to be no larger than 0.7 mm above major diameter of entry thread if it is a plain entry, and shall be tapered threads with not less than 3 threads or parallel threads with not less than five threads, with a tolerance class of 6H or better according to ISO 965-1 if it is a threaded entry.

**7. Earthing or Grounding**

Protective earthing (PE) conductor connection facilities shall allow for effective connection of at least one conductor whose cross sectional area will be according to the table below:

Cross sectional area of phase conductors, S (mm <sup>2</sup> )	Minimum cross sectional area of corresponding PE conductor (mm <sup>2</sup> )
$S \leq 16$	S
$16 < S \leq 35$	16
$S > 35$	0.5 S

Equipotential bonding connection facilities on the outside of electrical equipment shall provide effective connection of a conductor with a cross-sectional area of at least 4 mm<sup>2</sup>. When this connection facility is also intended to serve as the PE connection, the requirements of above table apply.

**8. Maintenance/Repair**

Operator of electrical equipment has to operate, supervise and maintain electrical equipment in good condition. The period of maintenance must be determined so that any non-conformity can be avoided. All assembly/dismantling and maintenance work must only be performed by trained technical personnel and in accordance with applicable code of practice.

- The equipment must not be opened when energised
- The gasket must be undamaged. If damaged, original part from Raychem RPG must be used.
- All cable glands and locknuts must be tighten and undamaged. If found damage, replace as necessary.
- Check for any signs of ingress in the enclosure and change the seal as required. Original seal from Raychem RPG must be used.
- Must ensure all connections facilities are tighten accordingly.
- Must check for any signs of damage which can affect the equipment performance.
- All parameters of initial operation must be taken into consideration before putting equipment into service after maintenance.

## 9. Schedule of Limitations

The following conditions are applied:

- All cable entry devices must be certified for protection concept 'eb' and 'tb' and all unused openings shall be fitted with suitable blanking elements with protection concept 'eb' and 'tb' so that minimum ingress protection of IP 64 is maintained.
- The suitability of all components / terminals employed shall be considered in the end use application.