


Product Information

Product Category	FLOORCARE
Unit Barcode	5016368081020
Outer Carton Barcode	
Commodity Code	8508110000
Country of Origin	CHINA
Primary Colour	BLACK
Finish	PLASTIC
Primary Material	PLASTIC
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	

General Product Specification

Voltage	230
Frequency	50
Wattage	1200
Rated Current	5.22
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	8
Class	CLASS II
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	342	355	422
Packaged Dimensions H x W x D (mm)	345	320	465
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			6.5
Unit Packaged Weight (Kg)			7.13
Carton Weight (Kg)			
EPS (Kg)		PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.027	Card / Paper (Kg)	1.11
Aluminium (Kg)		Steel (Kg)	

Category Specific Technical Information

Corded or Cordless	CORDED	Battery Charge Time	
Wet & Dry: YES	Bagged/BagBAGLESS	Battery Type	
Tube Material	STAINLESS STEEL	Battery EN Number	
Suitable Floor Types	CARPET & HARD FLOOR	Battery Level Indicator	
Cyclonic System		Battery Milli-Ampere-Hours	
Filter Type	HEPA	Battery Voltage	
Dust Capacity	15	Battery Watt-Hours	
Dirty Water Capacity	6	Battery Weight	
Clean Water Capacity	6	Air Flow Rate	108
Motor Type	AC	Cleaning Path Width	1000
Motor Max Capacity	1200	Handheld Vacuum Nozzle Width	
Maximum Suction Power	200	Cleaning Range	
Maximum Vacuum Suction	20	Hose Length	2
Number of Speed Settings		LED Lights	NO
Run Time High: Low:		Motorised Floorhead	NO
Allergy/Asthma Approval	NO	Noise Level	86
Lithium Battery Energy Capacity		Number of Accessories Included	
Number of Lithium Ion Cells		Adjustable Floorhead	NO