

## Horizontal quick-action clamp

With open clamping arm and angular base



### Application:


For quick and secure clamping on machine tables and appliances.

### Execution:

- Galvanised and passivated
- With red oil-resistant plastic handle
- Case-hardened and lubricated bearing bushes
- Stainless steel rivet
- Ergonomic, oil-resistant handle with large hand rest and soft components
- Protection against the loss of the clamping screw on the end of the clamping arm

### Delivery:

With tempered and galvanised thrust bolt



<b>Art. no.</b>	<b>26216 030</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	93336
<b>Size</b>	3
<b>Hole distance</b>	24 mm
<b>Hole distance 2</b>	28.5 mm
<b>Bore diameter</b>	6.8 mm
<b>Clamping height</b>	70 mm
<b>Retaining force</b>	1800 N
<b>Max. tensile force</b>	2500 N
<b>Height</b>	86.5 mm
<b>Length</b>	206 mm
<b>Thumbscrew size</b>	M8 x 45 mm
<b>Gross Weight</b>	0.389 kg
<b>Product Group</b>	260

### EAN

4020772093334