

### Product type designation



### MDS D424 transponder

TRANSPONDER MDS D424 FOR RF200/ RF300 ISO/ MOBY D  
 BUTTON ISO 15693 CHIP TYPE, FUJITSU MB89R118, 2000 BYTE  
 FRAM USER MEMORY 27 X 4 MM (DXH); -25 UP TO +85 DGR;  
 MINIMAL ORDER QUANTITY 20 PCS

### Wireless frequencies

Operating frequency / Rated value	13.56 MHz
-----------------------------------	-----------

### Electrical data

Range / maximum	300 mm; range is reader dependent: observe <a href="http://support.automation.siemens.com/WW/view/en/67384964">http://support.automation.siemens.com/WW/view/en/67384964</a>
Protocol / with radio transmission	ISO 15693
Transfer rate / with radio transmission / maximum	26.5 kbit/s
Product property / multitag-capable	Yes
Product component / Backup battery	No

### Memory

Type of memory	FRAM
Storage capacity / of the user memory	2000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2000 bytes, configuration memory 40 bytes
Number of read cycles / at ambient temperature < 40 °C / maximum	10000000000
Number of write cycles / at ambient temperature < 40 °C / maximum	10000000000
Data retention time / at ambient temperature < 40 °C / not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118

### Mechanical data

Material	Epoxy resin
----------	-------------

Color	black
Tightening torque / of the screw for securing the equipment / maximum	1 N·m
Mounting distance / relating to metal surfaces / recommended / minimum	25 mm

### Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> <li>during read/write access</li> </ul>	-25 ... +85 °C
<ul style="list-style-type: none"> <li>outside the read/write area</li> </ul>	-40 ... +100 °C
<ul style="list-style-type: none"> <li>during storage</li> </ul>	-40 ... +100 °C
Protection class IP	IP67 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	1000 m/s <sup>2</sup>
Resistance against vibration	200 m/s <sup>2</sup>

### Design, dimensions and weight

Height	4 mm
Diameter	27 mm
Net weight	5 g
Mounting type	M3 screw, gluing

### Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> <li>silicon-free</li> </ul>	Yes
<ul style="list-style-type: none"> <li>printable</li> </ul>	No

### Standards, specifications, approvals

MTBF	171 y
------	-------

### Accessories

accessories	Mounting support and spacer
-------------	-----------------------------

### Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> <li>to website: Selector SIMATIC NET SELECTION TOOL</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
<ul style="list-style-type: none"> <li>to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a>
<ul style="list-style-type: none"> <li>to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>to website: CAx Download Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**last modified:** 09.03.2015