

Indexable insert countersink, single tooth cutter

for universal use up to 1300 N/mm² with CC..06 and CC..09..

ATORN[®]

Application

180° countersinks with CC.. indexable inserts in the diameter range from 10.00–33.00 mm, in the material groups steel, stainless steel, non-ferrous metals, cast materials and special alloys for use in single part and series production.



Version

- backing material made from high-grade steel with clamping surface in line with DIN 1835B

Advantage

- precisely fitting inserts ensure optimum machining results even under difficult conditions
- universal use in all material groups
- cost-efficient tool in comparison with mono-block solutions

| | |
|---------------------------------------|-------------------|
| Art. No. | 11240 490 |
| Number of cutting edges | 1 PCS |
| Tool holding device | HB parallel shank |
| Cutting edge diameter | 19 mm |
| Cantilever length | 40 mm |
| Length | 95 mm |
| Min. pilot hole diameter | 6 mm |
| Shaft diameter | 16 mm |
| Suitable for indexable inserts | CC..09 |

EAN-Code

4050293112252