

Holder thread milling cutter dual-cutter steel straight shank HB

For using thread milling cutter inserts

ATORN[®]

Application


For using ground thread milling cutter inserts no. 13397.

Version

- Burnished steel tool holder with two insert seats

Advantage

- High process reliability and dimensional accuracy due to precise insert seating
- High-quality carrier material for very high service life requirements
- High machining speed due to two-tip geometry



Art. No.	13397 090
Tool holding device	HB parallel shank
Coolant supply	Internal
Suitable for indexable insert size	14
Cutting edge length	14 mm
Cutting edge diameter	20 mm
Suitable for min. diameter	26 mm
Shaft diameter	20 mm
Length	93 mm
Effective length of thread milling	41 mm

EAN-Code

4050293205268