




Flange Plate for NPT and NPK, Version A and B

Material: Steel C45, zinc-plated.

Mounting plate with metric fastening thread, for mounting on the end of the spindle.





Ordering details: e.g.: Prod. No. 475 000 15,
Flange plate for version A and B, Size 0

Product No.	Size	F ₁ mm	F ₂ mm	F ₃ mm	F ₄ mm	F ₅ mm	F ₆ mm	F ₇ mm	F ₈ mm	Weight kg
475 000 15	0	50	40	26	M10	16	7	4 x Ø7	M4	0,1
475 001 15	1	65	48	29	M12	20	7	4 x Ø9	M5	0,2
475 002 15	2	80	60	39	M14	20	8	4 x Ø11	M6	0,3
475 003 15	3	90	67	46	M20	23	10	4 x Ø11	M8	0,6
475 004 15	4	110	85	60	M30	30	15	4 x Ø13	M8	1,3

Travelling Nut for NPT Version C, with Trapezoidal Thread

Material: Bronze CuSn12-C-GC (2.1052).

Preferred installation position for compressive force: with the flange facing downwards (compressive load on the flange instead of tensile load on the screws).



Ordering details: e.g.: Prod. No. 475 000 11, Travelling
nut for Version C, with trapezoidal thread, Size 0

Product No.	Size	D4 mm	E ₁ mm	E ₂ mm	F ₁ mm	F ₂ ^{h9} mm	F ₃ mm	F ₄ mm	Mounting hole mm	Weight kg	Product No. Cardan Adapter KARA Page 518	Product No. Adapter Console KONA Page 518
475 000 16	0	Tr. 16x4	10	25	45	25	35	25	6 x Ø6	0,2	644 701 25	644 702 25
475 001 16	1	Tr. 18x4	12	44	48	28	38	28	6 x Ø6	0,3	644 701 28	644 702 28
475 002 16	2	Tr. 20x4	12	44	55	32	45	32	6 x Ø6	0,4	644 701 32	644 702 32
475 003 16	3	Tr. 30x6	14	46	62	38	50	38	6 x Ø7	0,7	644 701 38	644 702 38
475 004 16	4	Tr. 40x7	16	73	95	63	78	63	6 x Ø9	2,0	644 701 63	644 702 63

Travelling Nut for NPK Version C, with Ball Thread

Ordering details: e.g.: Prod. No. 475 001 LM1, Travelling nut for Version C, Size 1, with ball thread 16x5

