


TECHNICAL DATASHEET

Update : 25/02/2019

INTERNAL BORING BAR 93° SDUCR/L



Characteristics

Ref.	EAN	Diameter mm	Head length mm	Type of assembly	Type of tool tip attachment	Min reaming diameter mm
832739	3660338054440	10	100	Left	A10 SDUCL 07	13
832738	3660338054433	10	100	Right	A10 SDUCR 07	13
832741	3660338054464	12	125	Left	A12 SDUCL 07	16
832740	3660338054457	12	125	Right	A12 SDUCR 07	16
832742	3660338054471	16	150	Right	A16 SDUCR 07	20
832743	3660338054488	16	150	Left	A16 SDUCL 07	20
832745	3660338054501	20	180	Left	A20 SDUCL 11	25
832744	3660338054495	20	180	Right	A20 SDUCR 11	25
832747	3660338054525	25	200	Left	A25 SDUCL 11	32
832746	3660338054518	25	200	Right	A25 SDUCR 11	32