

MZE sleeve tensioning spindles

Without clamping sleeves




Application:

For inspection, light turning tasks, for grinding and balancing.

Execution:

- For holding between points
- An even and cylindrical tensioning force is achieved with the alternately slotted spreader sleeves.
- Case-hardened and ground
- Concentricity tolerance of 0.01 mm
- Sleeve tensioning spindles without clamping sleeves no. 22300



Art. no.	22300 010
Brand	RÖHM
Manufacturer Part Number	315002
Min./max. clamping range	12-15 mm
Length	125 mm
Gross Weight	0.251 kg
Product Group	205

EAN

4019208070292