

## Product information

# 02 07 200

## High Leverage Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Precise, minimal light gap between the gripping jaws to ensure optimal function of the cutting edges
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



### General

Article No.	02 07 200
EAN	4003773022299
Pliers	chrome-plated
Head	chrome-plated
Handles	with dipped insulation, VDE-tested
Weight	380 g
Dimensions	200 x 69 x 36 mm
Standard	DIN ISO 5746 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities hard wire (diameter)	Ø 2.8 mm
Cutting capacities piano wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple-stranded	Ø 13.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm <sup>2</sup>
VDE tested	yes

technical change and errors excepted