













| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]<br> | CONTACT PART NUMBERS    |   | CONTACT DESCRIP.                  | APPLIC. SPECIF.                                  |
|--|---|--|--|--|---|---|--|---|-----------------------------------|--|
|  |   |  |  |  |   |   | LOOSE PIECE<br>   | STRIP FORM<br>   |                                   |  |
| 91507-1<br>91507-3   | 0.20-0.50<br>[24-20]  | 1.14-1.78<br>[.045-.070]   | NO   | NO   | 3.56 ± 0.39<br>[.140 ± .0155]   | 0.84 ± 0.05<br>[.033 ± .002]  | 60789-[ ]<br>61276-[ ]   | 60598-[ ]<br>61119-[ ]  | .058 DIAMETER<br>PC CONTACT       | 114-1008   |
| 91526-1<br>91526-3   | 0.12-0.38<br>[26-22]<br>0.50-0.96<br>[20-18]  | 1.27-2.92<br>[.050-.115]   | YES  | NO   | 3.96 ± 0.38<br>[.156 ± .015]  | 0.71 ± 0.057<br>[.028 ± .002]<br>0.97 ± 0.057<br>[.038 ± .002]  | 350666-[ ]<br>640545-[ ]<br>640580-[ ]<br>641300-[ ]   | 350665-[ ]<br>350967-[ ]<br>350969-[ ]<br>641294-[ ]  | MINIATURE RECTANGULAR<br>CONTACTS | 114-1014   |
| 91531-1<br>91531-3   | 0.12-0.35 PIN<br>[26-22]<br>0.12-0.35 RECP<br>[26-22]   | 0.91-1.37<br>[.036-.054]   | YES  | YES  | 3.56 ± 0.38<br>[.140 ± .015]  | 0.76 ± 0.05<br>[.030 ± .002]  | 104505-3<br>104505-5<br>104505-7<br><br>531216-2 104480-7<br>531216-4 104480-8<br>530553-3 104480-9<br>530553-5 1-104480-4<br>530553-7 1-104480-5<br>531224-7 1-104480-6 | 104505-2<br>104505-4<br>104505-6<br><br>531216-1 104480-1 1-104480-7<br>531216-3 104480-2<br>530553-3 104480-3<br>530553-5 104480-4<br>530553-7 1-104480-2<br>531224-6 1-104480-3 | TANDEM SPRING<br>Contacts         | 114-25021  |
| 91534-1<br>91534-3   | 0.12-0.24<br>[26-24]  | 0.64-1.27<br>[.025-.050]   | YES  | NO   | 3.96 ± 0.38<br>[.156 ± .015]  | 0.71 ± 0.05<br>[.028 ± .002]  | 640579-[ ]<br>794001-[ ]   | 350968-[ ]<br>794000-[ ]  | MINIATURE RECTANGULAR<br>CONTACTS | 114-1014   |
| 91535-1<br>91535-3   | 0.20-0.35<br>[24-22]<br>0.50-0.56<br>[20]   | 1.22-2.03<br>[.048-.080]   | YES  | NO   | 3.56 ± 0.38<br>[.140 ± .015]  | 0.84 ± 0.05<br>[.033 ± .002]<br>0.99 ± 0.05<br>[.039 ± .002]  | 531477-3 583853-9<br>531477-5 1-583853-1<br>583853-4<br>583853-5   | 531477-1 583853-3<br>531477-2 583853-7<br>531477-4 583853-8<br>583853-1 1-583853-0<br>583853-2 1-583853-3   | TWIN LEAF<br>CONTACTS             | 114-9004   |
| 91537-1<br>91537-3   | 0.12-0.22<br>[26-24]<br>0.30-0.35<br>[22]   | 1.02-1.42<br>[.040-.056]<br>1.02-1.75<br>[.040-.069]<br>1.02-1.42<br>[.040-.056]<br>1.02-1.75<br>[.040-.069]         | NO   | NO   | 3.18 ± 0.38<br>[.125 ± .015]  | 0.622 ± .038<br>[.0245 ± .0015]<br>0.71 ± 0.05<br>[.028 ± .002]   | 86561-[ ] 88067-[ ]<br>86571-[ ] 181270-[ ]<br>86658-2<br>86657-2<br>86561-[ ] 88067-[ ]<br>86571-[ ] 181270-[ ]<br>86658-2<br>86657-2                                   | 86557-[ ] 88067-2<br>86566-[ ]<br>86557-[ ] 88067-2<br>86566-[ ]<br>86656-2<br>86655-2  | FLEXIBLE FLAT CABLE<br>CONNECTORS | 114-16003<br>114-16007<br>114-16015<br>114-20004 |
| 91538-1<br>91538-3   | 0.05-0.56<br>[30-20]  | 0.76-2.16<br>[.030-.085]   | NO   | NO   | 5.16 ± 0.38<br>[.203 ± .015]  | 1.09 ± 0.05<br>[.043 ± .002]  | SEE INSTRUCTION SHEET<br>408-10274   |   | TYPE II SCREW MACHINE<br>CONTACT  | 114-10026  |


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.











 -1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.


4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.

2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.


### CERTI-CRIMP II DATA SHEET

|                   |  |  |  |  |  |                            |  |                 |  |
|-------------------|--|--|--|--|--|----------------------------|--|-----------------|--|
| DIMENSIONS:<br>mm |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | DWN: M. YOUNGER 21FEB2012  |  | MATERIAL: -                |  | HEAT TREAT: -   |  |
| 0 PLC ± -         |  | 1 PLC ± -                              |  | CHK: B.A. WOLFE 22FEB2012  |  | APVD: B.A. WOLFE 22FEB2012 |  | TE Connectivity |  |
| 2 PLC ± -         |  | 3 PLC ± -                              |  | NAME: B.A. WOLFE   |  | SCALE: -                   |  | SIZE: A1        |  |
| 4 PLC ± -         |  | ANGLES: -                              |  | SURFACE TEXTURE:  |  | DRAWING NO: 1583011        |  | SHEET: 1 of 8   |  |
| P LTR             |  | REVISION RECORD                        |  | DATE: 08/2016  |  | DWN: AW                    |  | CAM             |  |

| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]<br> | CONTACT PART NUMBERS  |   |   |                      | CONTACT DESCRIP.                            | APPLIC. SPECIF. |
|--|---|--|--|--|---|---|--|---|---|----------------------|---|-----------------|
|  |   |  |  |  |   |   | LOOSE PIECE<br>       |   | STRIP FORM<br> |                      |   |                 |
| 91539-1<br>91539-3   | 0.30-0.89 [22-18]   | -  | NO   | NO   | 6.35 ± 0.38 [250 ± .015]  | 1.60 ± 0.05 [0.63 ± .002]   | PIN -  | SOCKET 201751-[ ]   | COLOR: GREEN BARREL<br>BLUE SHOULDER  |                      | TYPE II SCREW MACHINE CONTACT               | 114-10026       |
|  | 2x0.75 [2x18]   | -  |  |  |   |   | PIN 202725-[ ]   | SOCKET 202726-[ ]   | COLOR: BLUE SHOULDER  |                      |   |                 |
|  | 0.75-1.42 [18-16]   | -  |  |  |   |   | PIN 200681-[ ]<br>200336-[ ]<br>204274-[ ]<br>204219-[ ]<br>207893-[ ]                                   | SOCKET 201589-[ ]<br>200333-[ ]<br>207896-[ ]<br>130743-1 | COLOR: BLUE BARREL<br>BLUE SHOULDER   |                      |   |                 |
|  | 2.00-2.27 [14]  | -  |  |  |   |   | PIN 201645-[ ]<br>201570-[ ]   | SOCKET 201568-[ ]   | COLOR: VIOLET BARREL<br>BLUE SHOULDER   |                      |   |                 |
| 91540-1<br>91540-3   | 0.12-0.35 [26-22]   | 0.91-1.42 [0.36-.056]  | YES  | NO   | 3.56 ± 0.38 [140 ± .015]  | 0.76 ± 0.05 [0.30 ± .002]   | 530553-5   | 531216-2  | 530553-1  | 530553-6             | TANDEM SPRING & MINI-TANDEM SPRING CONTACTS | 114-25021       |
|  | 0.03-0.09 [32-28]   | 0.64-1.37 [0.25-.054]  |  |  |   |   | 530553-7   | 531216-4<br>531224-7                                      | 530553-2<br>530553-4  | 531216-1<br>531216-3 |   |                 |
| 91544-1<br>91544-3   | 0.20-0.35 [24-22]   | 1.58 MAX [0.62] MAX  | YES  | NO   | 3.96 ± 0.38 [156 ± .015]  | 0.724 ± 0.051 [0.285 ± .002]  | 164169-[ ]   | 203802-[ ]  | 164153-[ ]  | 203801-[ ]           | TYPE XI CONTACT                             | 114-10002       |
|  | 0.50-0.56 [20]  |  |  |  |   |   | 164170-[ ]   | 203816-[ ]  | 164155-[ ]  | 203815-[ ]           |   |                 |
| 91546-1<br>91546-3   | 0.50-0.89 [20-18]   | 2.03-2.54 [0.80-1.00]  | NO   | NO   | 4.76 ± 0.38 [188 ± .015]  | 1.42 ± 0.05 [0.56 ± .002]   | 41667  |   | 41650   |                      | TAPER PIN CONTACT                           | 114-7006        |
| 91547-1<br>91547-3   | 0.20-0.35 [24-22]   | 1.02-1.52 [0.40-.060]  | NO   | NO   | 3.18 ± 0.38 [125 ± .015]  | 0.89 ± 0.05 [0.35 ± .002]   | 41661<br>41662   | 41663   | 41278<br>41640  | 41646<br>66113-3     | TAPER PIN CONTACT                           | 114-7006        |
| 91555-1<br>91555-3   | 0.20-0.56 [24-20]   | 1.02-1.78 [0.40-.070]  | NO   | NO   | 2.92-3.68 [115-145]   | 0.991 ± 0.038 [0.39 ± .0015]  | 66010-[ ]<br>531586-6  |   | 66005-[ ]<br>531586-3   |                      | AMP-BLADE RECEPTACLE CONTACT                | 108-9202        |
|  | 2x0.2 DR 2x0.3 [2x24 DR 2x22]   | 2.79 [110] MAX TOTAL   |  |  |   |   |  |   |   |                      |   |                 |


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.


2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.

 -1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY.  
-3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.











4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.


### CERTI-CRIMP II DATA SHEET


|  |          |   |                      |
|--|----------|---|----------------------|
| DWG: M. YOUNGER 21FEB2012                                      |          | MATERIAL: -   | HEAT TREAT: -        |
| CHK: B.A. WOLFE 22FEB2012                                      |          |  TE Connectivity |                      |
| APVD: B.A. WOLFE 22FEB2012                                     |          |   |                      |
| NAME: CERTI-CRIMP II TOOL DATA SHEET<br>MISCELLANEOUS CONTACTS |          |   |                      |
| SCALE: -   | SIZE: A1 | DRAWING NO: 1583011   | SHEET 2 of 8 REV F15 |

|                |        |  |        |
|----------------|--------|--|--------|
| DIMENSIONS: mm |        | TOLERANCES UNLESS OTHERWISE SPECIFIED:   |        |
| 0 PLC          | ± .05  | 1 PLC  | ± .02  |
| 1 PLC          | ± .01  | 2 PLC  | ± .01  |
| 2 PLC          | ± .005 | 3 PLC  | ± .005 |
| 3 PLC          | ± .002 | 4 PLC  | ± .002 |
| ANGLES: -      |        | SURFACE TEXTURE:  |        |

|   |    |                 |      |     |      |
|---|----|-----------------|------|-----|------|
| P | TR | REVISION RECORD | DATE | DWG | APVD |
| - | -  | SEE SHEET 1     | -    | -   | -    |

| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]<br> | CONTACT PART NUMBERS  |         |   |   | CONTACT DESCRIP.        | APPLIC. SPECIF. |
|--|---|--|--|--|---|---|---|---------|---|---|-------------------------|-----------------|
|  |   |  |  |  |   |   | LOOSE PIECE<br>      |         | STRIP FORM<br> |   |                         |                 |
| 91354-1  | 1.94-2.15 [14]  | 2.18-3.94 [.086-.155]  | NO   | NO   | 4.8-5.6 [.189-.220]   | 1.70 ± 0.05 [.067 ± .002]   | 9-1437846-0   |         |   | .040" [DUAL CONTACT] SBEC 1 MM TERMINAL | 114-13039               |                 |
| 91355-1  | 0.32-0.38 [22]  | 1.50-1.75 [.059-.069]  | NO   | NO   | 4.8-5.6 [.189-.220]   | 1.10 ± 0.05 [.043 ± .002]   | 9-1437846-1   |         |   | .040" [DUAL CONTACT] SBEC 1 MM TERMINAL | 114-13039               |                 |
|  | 0.81-0.96 [18]  | 1.70-3.00 [.067-.118]  |  |  |   | 1.45 ± 0.05 [.057 ± .002]   | 9-1437846-2   |         |   |   |                         |                 |
| 91356-1  | 1.28-1.42 [16]  | 2.18-2.41 [.086-.095]  | NO   | NO   | 4.8-5.6 [.189-.220]   | 1.32 ± 0.05 [.052 ± .002]   | 1456004-1   |         |   | 1 MM TERMINAL                           | 114-13039               |                 |
| 91357-1  | 0.50-0.60 [20]  | 1.70-1.93 [.067-.076]  | NO   | NO   | 4.8-5.6 [.189-.220]   | 1.05 ± 0.05 [.041 ± .002]   | 1456004-2   |         |   | 1 MM TERMINAL                           | 114-13039               |                 |
|  | 0.81-0.96 [18]  | 1.90-2.25 [.075-.089]  |  |  |   | 1.15 ± 0.05 [.045 ± .002]   | 1456004-1   |         |   |   |                         |                 |
| 91599-1  | 0.20-0.22 [24]  | 0.96-1.12 [.038-.044]  | NO   | NO   | 2.5-3.3 [.100-.130]   | 0.79 ± 0.05 [.031 ± .002]   | 1604735-1   |         |   | FUSE CLIP                               | N/A                     |                 |
| 1725061-1  | 0.30-0.35 [22]  | 1.34-1.60 [.053-.063]  | NO   | NO   | 3.8-4.8 [.150-.189]   | 1.55 ± 0.13 [.061 ± .005]   | ASCO PN: 280019-001   |         |   | ASCO REDHAT                             | N/A                     |                 |
| 1804573-1  | 0.50-0.56x2 [20x2]  | 1.27-1.83 [.050-.072]  | NO   | NO   | 2.9-3.7 [.115-.145]   | 1.11 ± 0.05 [.043 ± .002]   | 66026-2   | 66021-2 |   | AMP BLADE RECEPT.                       | 108-9201                |                 |
| 1804573-3  |   | 1.73-2.29 [.065-.090]  |  |  |   | 0.99 ± 0.05 [.039 ± .002]   |   |         |   |   |                         |                 |
| 1213783-1  | 0.12-0.37 (26-22)   | 1.20-1.90 (.047-.075)  | NO   | NO   | 3.2 ± 0.5 (.12 ± .02)   | 0.83 ± 0.04 (.033 ± .002)   | 175153  | 175155  | 175149  | 175151                                  | UNIVERSAL POWER CONTACT | 114-5142        |
|  | 0.50-0.89 (20-18)   | 1.70-2.70 (.067-.106)  |  |  |   | 1.13 ± 0.05 (.044 ± .002)   | 175154  | 175156  | 175150  | 175152                                  |                         |                 |
|  | 1.25-1.42 (16)  | 2.50-3.30 (.098-.130)  |  |  |   | 1.43 ± 0.05 (.056 ± .002)   |   |         |   |   |                         |                 |


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

 -1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.

2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.

### CERTI-CRIMP II DATA SHEET

|   |          |   |                      |
|---|----------|---|----------------------|
| DWG: M. YOUNGER 21FEB2012                                   |          | MATERIAL: -   | HEAT TREAT: -        |
| CHK: B.A.WOLFE 22FEB2012                                    |          |  TE Connectivity |                      |
| APVD: B.A. WOLFE 22FEB2012                                  |          |   |                      |
| NAME: CERTI-CRIMP II TOOL DATA SHEET MISCELLANEOUS CONTACTS |          |   |                      |
| SCALE: -  | SIZE: A1 | DRAWING NO: 1583011   | SHEET 3 of 8 REV F15 |

|       |      |
|-------|------|
| 0 PLC | ± .- |
| 1 PLC | ± .- |
| 2 PLC | ± .- |
| 3 PLC | ± .- |
| 4 PLC | ± .- |

| TOOL NUMBER<br>        | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br>         | INSULATION DIAMETER<br>mm [in.]<br>                  | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]<br>                                     | CONTACT PART NUMBERS            |                               | CONTACT DESCRIP.                                 | APPLIC. SPECIF.        |
|------------------------|--|--|-----------------|------------------|------------------------------|--|---------------------------------|-------------------------------|--|------------------------|
|                        |  |  |                 |                  |                              |  | LOOSE PIECE<br>                 | STRIP FORM<br>                |  |                        |
| 1901760-1<br>1901760-3 | 0.30-0.56<br>[22-20]                           | 1.5-2.4<br>[.059-.094]                               | NO              | NO               | 4.0 ± 0.2<br>[.156 ± .008]   | 0.99 ± 0.14<br>[.039 ± .003]                                     | 1-170321-1                      | 1-170291-1                    | DUAL LINK INTERLOCK CONN.                        | 114-5045               |
| 1901771-1<br>1901771-3 | 0.50-0.96<br>[20-18]<br>0.12-0.38<br>[26-22]   | 1.27-2.92<br>[.050-.115]                             | YES             | NO               | 4.0 ± 0.4<br>[.156 ± .015]   | 0.97 ± 0.05<br>[.039 ± .002]<br>0.71 ± 0.05<br>[.028 ± .002]     | 350037<br>350036                | 350019<br>350018              | MINIATURE RECTANGULAR CONTACT                    | 114-1014               |
| 1901786-1<br>1901786-3 | 0.03-0.09<br>[32-28]                           | 0.64-1.52<br>[.025-.060]<br>0.64-1.37<br>[.025-.054] | YES             | NO               | 3.96-3.18<br>[.156-.125]     | 0.53 ± 0.05<br>[.021 ± .002]                                     | 530901-3<br>104506-[ ]          | 530901-2<br>104506-[ ]        | MINI TANDEM SPRING RCPT<br>AMPMODU MTE PIN       | 114-25021<br>114-25026 |
| 1901798-1<br>1901798-3 | 0.20-0.38<br>[24-22]<br>0.5-0.6<br>[20]        | 0.97-1.57<br>[.038-.062]<br>1.27-2.54<br>[.050-.100] | YES             | NO               | 3.96<br>[.156]               | 0.89 ± 0.05<br>[.035 ± .002]<br>1.02 ± 0.05<br>[.040 ± .002]     | -                               | 867052-[ ]                    | LOCKING CLIP .025-IN. SQUARE CONTACT             | 114-25006              |
| 1901829-1<br>1901829-3 | INSULATION PIERCING<br>SEE INSULATION DIAMETER | 1.40 [.055]<br>1.02 [.040]                           | NO              | NO               | USE UNSTRIPPED WIRE          | 1.27 ± 0.05<br>[.050 ± .002]<br>1.17 ± 0.05<br>[.046 ± .002]     | 102348-2<br>102348-3            | 87107-5<br>87107-6            | MOD IV CRIMP SNAP-IN RCPT                        | 114-25003              |
| 1901957-1<br>1901957-3 | 0.05-0.15<br>[30-26]<br>0.12-0.35<br>[26-22]   | 1.0-1.9<br>[.039-.075]<br>0.9-1.5<br>[.035-.059]     | YES             | NO               | 2.5 ± 0.5<br>[.098 ± .020]   | 0.71-0.86<br>[.028-.034]<br>0.59-0.73<br>[.023-.029]             | 171612-[ ]<br>171611-[ ]        | 171610-[ ]<br>171609-[ ]      | AMP-ULTREX 2.5mm/2.54mm PITCH RECEPTACLE CONTACT | 114-5077               |
| 1901963-1<br>1901963-3 | 1.28-2.15<br>[16-14]<br>0.50-0.96<br>[20-18]   | 3.3-4.6<br>[.130-.180]<br>2.5-4.6<br>[.100-.180]     | YES             | NO               | 6.35 ± 1.60<br>[.250 ± .062] | 1.68 ± 0.08<br>[.066 ± .003]<br>1.40 ± 0.08<br>[.055 ± .003]     | SOCKET PIN<br>350388-1 350389-1 | SOCKET PIN<br>61626-1 61627-1 | .140 MATE-N-LOK PIN AND SOCKET                   | 114-1007               |
| 1976150-1              | 0.50-1.00<br>[24-20]<br>0.21-0.56<br>[32-26]   | 1.80 MAX<br>[.071 MAX]<br>1.27 MAX<br>[.050 MAX]     | YES             | NO               | 4.37 ± 0.25<br>[.172 ± .010] | 0.94 ± 0.05<br>[.037 ± .002]<br>0.978 ± 0.050<br>[.0385 ± .0020] | -                               | 86497-2<br>86008-1            | HI PRESSURE AMPMODU (INVERTED)                   | 114-25010              |
| 2217748-1              | 0.80-0.50<br>[18-20]<br>1.40<br>[16]           | 1.7-2.7<br>[.067-.106]                               | YES             | NO               | 5.10 ± 0.40<br>[.200 ± .016] | 1.22 ± 0.05<br>[.048 ± .002]<br>1.40 ± 0.050<br>[.055 ± .0020]   | 770854-1                        | 770520-1                      | AMPSEAL  | 114-16016              |

LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.











-1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY.  
-3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.


4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.

### CERTI-CRIMP II DATA SHEET


|                                  |  |   |      |                           |                 |                     |
|----------------------------------|--|---|------|---------------------------|-----------------|---------------------|
| DIMENSIONS:<br>mm                |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:                        |      | DWG: M. YOUNGER 21FEB2012 | MATERIAL: -     | HEAT TREAT: -       |
| <br>ANGLE: -<br>SURFACE TEXTURE: |  | 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± - |      | CHK: B.A. WOLFE 22FEB2012 | TE Connectivity |                     |
| APVD: B.A. WOLFE 22FEB2012       |  | NAME: CERTI-CRIMP II TOOL DATA SHEET MISCELLANEOUS CONTACTS   |      | SCALE: -                  | SIZE: A1        | DRAWING NO: 1583011 |
| P LTR                            |  | REVISION RECORD   | DATE | DWG                       | APVD            | SHEET 4 of 8        |


THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO 1583011

| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]<br> | CONTACT PART NUMBERS  |   | CONTACT DESCRIP.                             | APPLIC. SPECIF. |
|--|---|--|--|---|---|---|---|---|--|-----------------|
|  |   |  |  |   |   |   | LOOSE PIECE<br>      | STRIP FORM<br> |  |                 |
| 1901557-1  | 0.50-0.56 [ 20 ]  | 2.20-2.60 [.087-.102]  | NO   | NO  | 4.0-5.0 [.157-.197]   | 1.285 ± 0.065 [.0505 ± .0025]   | 170112<br>170113  | 170099-2<br>170100-2  | .079 (2.0mm) DIA PIN & RECEPTACLE            | 114-5019        |
|  | 0.75-0.89 [ 18 ]  |  |  |   |   | 1.310 ± 0.090 [.0515 ± .0035]   |   |   |  |                 |
| 1901557-3  | 1.25-1.42 [ 16 ]  | 2.70-3.50 [.106-.138]  | NO   | NO  | 4.5-7.0 [.177-.276]   | 1.645 ± 0.050 [.0652 ± .0020]   | 170292<br>170293<br>171654  | 170279-1<br>170280-1<br>172786-1  | .079 (2.0mm) DIA PIN & RECEPTACLE, LANCELESS | 114-5039        |
|  | 2.00-2.27 [ 14 ]  |  |  |   |   | 1.690 ± 0.090 [.0665 ± .0035]   |   |   |  |                 |
| 1976577-1  | 0.80-1.24 [ 20-18 ]   | 1.37-1.88 [.054-.074]  | NO   | NO  | 2.92-3.68 [.115-.145]   | 1.35 ± 0.05 [.053 ± .002]   | 66169<br>66168  | 66144<br>66143  | AMP-TAB CONTACTS                             | 108-5039        |
| 1976577-3  | 0.40-0.64 [ 26-22 ]   | 0.89-1.37 [.035-.054]  |  |   |   | 0.94 ± 0.50 [.037 ± .002]   |   |   |  |                 |
| 2031245-1  | 0.50-0.90 [ 20-18 ]   | 1.27-1.65 [.050-.065]  | NO   | NO  | 3.18-3.96 [.125-.156]   | 1.029 ± 0.051 [.0405 ± .002]  | 167730-1<br>164715-1  | -<br>-  | AMP-LEAF                                     | 114-9003        |
| 2031245-3  | 0.20-0.40 [ 24-22 ]   | 0.89-1.40 [.035-.055]  |  |   |   | 0.775 ± 0.051 [.0305 ± .002]  |   |   |  |                 |
| 2031200-1  | 0.20-0.22 [24]  | 1.02 [.040]  | NO   | NO  | 3.56 ± 0.39 [.140 ± .015]   | 0.84 ± 0.05 [.033 ± .002]   | 60789<br>61276  | 60598<br>61119  | .058 DIA PC CONTACT                          | 114-1008        |
| 2031200-3  |   |  |  |   |   |   |   |   |  |                 |
| 2063834-1  | 0.5-0.6 [ 20 ]  | 1.8-2.1 [.071-.083]  | YES  | NO  | 4.00-5.00 [.157-.197]   | 0.89-1.05 [.035-.041]   | 179419-1<br>179420-1<br>1376702-1   | -   | .040 III UNSEALED RECEPTACLE CONTACT         | 114-5217        |
| 2063834-3  | 0.8-0.9 [ 18 ]  |  |  |   |   | 0.89-1.08 [.035-.043]   |   |   |  |                 |
|  | 1.25-14.42 [ 16 ]   |  |  |   |   | 1.06-1.40 [.042-.055]   |   |   |  |                 |
| 2063850-1  | 0.30-0.89 [22-18]   | 1.1-1.8 [.043-.071]  | YES  | NO  | 4.00-5.00 [.157-.197]   | 0.78-1.15 [.031-.045]   | 1376700<br>1376701  | 316836<br>316837  | .040 III UNSEALED RECEPTACLE CONTACT         | 114-5217        |
| 2063850-3  |   |  |  |   |   |   |   |   |  |                 |
| 2063811-1  | -   | 0.9-3.5 [.036-.138]  | NO   | NO  | -   | -   | 328854 328858<br>328855 328859<br>328856 328860<br>328857 328861  | -   | PRE-INSULATED SPARE WIRE CAP                 | -               |
| 2063811-3  |   |  |  |   |   |   |   |   |  |                 |
| 2063857-1  | 22 OR 20 OR (2)24   | 1.52-2.29 [.060-.090]  | NO   | NO  | 3.56±0.40 [.140±.015]   | 0.94 ± 0.05 [.037 ± .002]   | 640024-1  | 640259-1  | .058 DIA PC CONTACT                          | 114-1008        |
|  | 18 OR (2)20 OR (2)22  |  |  |   |   | 1.24 ± 0.05 [.049 ± .002]   |   |   |  |                 |


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.










 -1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.


 THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.


### CERTI-CRIMP II DATA SHEET

|   |          |   |                      |
|---|----------|---|----------------------|
| DWN: M. YOUNGER 21FEB2012                                   |          | MATERIAL: -   | HEAT TREAT: -        |
| CHK: B.A.WOLFE 22FEB2012                                    |          |  TE Connectivity |                      |
| APVD: B.A. WOLFE 22FEB2012                                  |          |   |                      |
| NAME: CERTI-CRIMP II TOOL DATA SHEET MISCELLANEOUS CONTACTS |          |   |                      |
| SCALE: -  | SIZE: A1 | DRAWING NO: 1583011   | SHEET 5 of 8 REV F15 |

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS THE PROPERTY OF TE CONNECTIVITY AND IS NOT TO BE DISCLOSED, REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT AUTHORIZATION FROM TE CONNECTIVITY.

| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]  | CONTACT PART NUMBERS  |   | CONTACT DESCRIP.             | APPLIC. SPECIF. |
|--|---|--|--|---|---|---|--|---|------------------------------|-----------------|
|  |   |  |  |   |   |   | LOOSE PIECE<br>       | STRIP FORM<br> |                              |                 |
| 2119536-1<br>2119536-3   | 0.03 [32]<br>0.50-0.06 [30]<br>0.08-0.09 [28]   | 0.4-0.7 [.016-.028]<br>0.5-0.8 [.020-.031]   | YES  | YES   | 1.0-1.2 [.04-.05]   | 0.405 ± 0.025 [.0159 ± .0010]<br>0.419 ± 0.025 [.0165 ± .0010]<br>0.460 ± 0.025 [.0181 ± .0010] | -  | 1734597-1   | 1.0 WIRE TO BOARD CONNECTOR  | 114-57020       |
| 2119537-1<br>2119537-3   | 0.03 [32]<br>0.05-0.06 [30]<br>0.08-0.09 [28]   | 0.9-1.2 [.035-.047]  | YES  | YES   | 0.9-1.3 [.04-.05]   | 0.485 ± 0.025 [.0190 ± .0010]<br>0.505 ± 0.025 [.0200 ± .0010]<br>0.535 ± 0.025 [.0210 ± .0010] | -  | 1734193-1   | 1.25 WIRE TO BOARD CONNECTOR | 114-57016       |
| 2119538-1<br>2119538-3   | 0.05-0.06 [30]<br>0.08-0.12 [28-26]<br>0.20 [24]  | .089-1.50 [.035-.059]  | NO   | YES   | 1.9-2.5 [.08-.10]   | 0.550 ± 0.025 [.022 ± .0010]<br>0.550 ± 0.025 [.022 ± .0010]<br>0.580 ± 0.025 [.023 ± .0010]    | -  | 1775442-1   | 2.0 WIRE TO BOARD CONNECTOR  | 114-57011       |
| 2119539-1<br>2119539-3   | 0.05 [30]<br>0.08-0.14 [28-26]<br>0.22 [24]   | .089-1.50 [.035-.059]  | YES  | YES   | 1.9-2.5 [.08-.10]   | 0.545 ± 0.025 [.0215 ± .0010]<br>0.584 ± 0.025 [.023 ± .0010]<br>0.645 ± 0.025 [.0255 ± .0010]  | -  | 440132-1<br>1735801-1   | 2.0 WIRE TO BOARD CONNECTOR  | 114-57011       |
| 1752794-1  | 0.20-0.35 [24-22]<br>0.50-0.56 [20]   | -  | NO   | NO  | 3.1-3.6 [.12-.14]   | 0.94 ± 0.05 [.037 ± .002]<br>1.07 ± 0.05 [.042 ± .002]  | -  | 42869-6   | .040 PIN RECEPT              | 114-2083        |
| 1976156-1  | .013 [26]<br>0.20-0.22 [24]   | 0.80-0.95 [.031-.037]<br>.090-1.20 [.035-.047]   | NO   | YES   | 3.25-3.55 [.13-.14]   | 0.61 ± 0.025 [.024 ± .001]<br>0.66 ± 0.025 [.026 ± .001]  | 1-211449-1<br>1-211449-2<br>1-211449-6   | 1-1703930-1<br>1-1703930-2<br>1-1703930-6   | NAND MQS                     | 114-18858       |
| 1976157-1  | 0.35 [22]<br>0.35 [22]  | 1.0-1.2 [.039-.047]<br>1.2-1.3 [.047-.051]   | NO   | YES   | 3.25-3.55 [.13-.14]   | 0.82 ± 0.025 [.032 ± .001]<br>0.82 ± 0.025 [.032 ± .001]  | 1-2112449-1<br>1-2112449-2<br>1-2112449-6  | 1-1703930-1<br>1-1703930-2<br>1-1703930-6   | NAND MQS                     | 114-18858       |


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

 -1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.










2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.


## CERTI-CRIMP II DATA SHEET

|   |     |  |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
|---|-----|--|-----|---|---|-----|-----|---|-----|-----|---|-----|-----|---|-----|-----|--|--|--------|---|-----------------|---|----------------------|--|
| DWN: M. YOUNGER 21FEB2012   |     | MATERIAL: -                            |     | HEAT TREAT: -   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| CHK: B.A. WOLFE 22FEB2012   |     | APVD: B.A. WOLFE 22FEB2012             |     |  TE Connectivity |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| NAME: B.A. WOLFE  |     | DRAWING NO: 1583011                    |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| DIMENSIONS: mm  |     | TOLERANCES UNLESS OTHERWISE SPECIFIED: |     | SCALE: -  |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| <table border="1" style="font-size: small;"> <tr><td>0</td><td>PLC</td><td>± .</td></tr> <tr><td>1</td><td>PLC</td><td>± .</td></tr> <tr><td>2</td><td>PLC</td><td>± .</td></tr> <tr><td>3</td><td>PLC</td><td>± .</td></tr> <tr><td>4</td><td>PLC</td><td>± .</td></tr> </table> |     | 0                                      | PLC | ± .   | 1 | PLC | ± . | 2 | PLC | ± . | 3 | PLC | ± . | 4 | PLC | ± . | <table border="1" style="font-size: small;"> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>SURFACE TEXTURE</td><td>√</td></tr> </table> |  | ANGLES | ± | SURFACE TEXTURE | √ | SHEET 6 of 8 REV F15 |  |
| 0   | PLC | ± .                                    |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| 1   | PLC | ± .                                    |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| 2   | PLC | ± .                                    |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| 3   | PLC | ± .                                    |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| 4   | PLC | ± .                                    |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| ANGLES  | ±   |  |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| SURFACE TEXTURE   | √   |  |     |   |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |
| P LTR   |     | REVISION RECORD                        |     | DATE  |   |     |     |   |     |     |   |     |     |   |     |     |  |  |        |   |                 |   |                      |  |



THIS DRAWING IS A CONTROLLED DOCUMENT. PART NO 1583011

| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]       | CONTACT PART NUMBERS  |   | CONTACT DESCRIP.                                     | APPLIC. SPECIF.  |                            |
|--|---|--|--|---|---|--------------------------------|--|---|--|------------------|----------------------------|
|  |   |  |  |   |   |                                | LOOSE PIECE<br>       | STRIP FORM<br> |  |                  |                            |
| 2217655-1  | 0.32-0.38 [22]  | 1.7-2.9 [.67-.114]   | YES  | NO  | 2.69-3.30 [.106-.130]   | 1.00 ± 0.05 [.039 ±.002]       | 1744395-1  | 1744144-1   | ECONOMY POWER II                                     | 114-13265        |                            |
|  | 0.50-0.60 [20]  |  |  |   |   | 1.10 ± 0.05 [.043 ±.002]       |  |   |  |                  |                            |
|  | 0.81-0.89 [18]  |  |  |   |   | 1.15 ± 0.05 [.043 ±.002]       |  |   |  |                  |                            |
| 2217660-1  | 0.50-0.60 [20]  | 1.7-2.9 [.67-.114]   | YES  | NO  | 2.46-2.84 [.097-.112]   | 1.12 ± 0.05 [.044 ±.002]       | 1744396-1  | 1744201-1   | ECONOMY POWER II                                     | 114-13265        |                            |
|  | 0.81-0.89 [18]  |  |  |   |   | 1.27 ± 0.05 [.050 ±.002]       |  |   |  |                  |                            |
|  | 1.25-1.42 [16]  |  |  |   |   | 1.47 ± 0.05 [.058 ±.002]       |  |   |  |                  |                            |
| 2217742-1  | 0.50-0.90 [20-18]   | 1.85-2.29 [.073-.090]  | YES  | NO  | 3.18-3.56 [.125-.156]   | 1.092 ± 0.051 [.043 ±.002]     | 583875-3<br>583875-6<br>5-583875-6   | 583875-2<br>583875-5<br>5-583875-5  | TWIN LEAF CONTACT                                    | 114-9004         |                            |
|  | 1.25-1.42 [16]  |  |  |   |   | 1.346 ± 0.051 [.053 ±.002]     |  |   |  |                  |                            |
| 2217754-1  | 0.30-1.00 [2X22-1X18]   | 2X22=3.05 MAX [.120 MAX]   | NO   | NO  | 3.18-3.56 [.125-.156]   | 1.1304 ± 0.038 [.0445 ±.0015]  | 42840-[ ]<br>583272-[ ]<br>583989-[ ]  | 42717-[ ] [ ]-583361-[ ]<br>60030-[ ] 58355-[ ]<br>583271-[ ] [ ]-583989-[ ]                      | AMP LEAF CONTACT                                     | 114-9003         |                            |
|  | 0.30-0.60 [22-20]   | 1X18=1.65-2.03 [.065-.080]   |  |   |   | 0.9779 ± 0.0381 [.0385 ±.0015] |  |   |  |                  |                            |
| 2217766-1  | 0.32-0.60 [22-20]   | 1.27-2.54 [.50-.100]   | YES  | NO  | 3.96 [.156]   | 1.02 ± 0.05 [.040 ±.002]       | 87278-[ ]  | 87269-[ ]   | LOCKING CLIP CONTACT<br>.031 X .062                  | 114-25008        |                            |
|  | 0.80-0.90 [18]  |  |  |   |   | 1.22 ± 0.05 [.048 ±.002]       |  |   |  |                  |                            |
| 2280413-1  | 0.85-0.87 [18]  | -  | NO   | YES   | 1.60 [.063]   | 1.15 ± 0.05 [.0153 ±.002]      | -  | RECPT-2271279-[ ]<br>PIN-2271283-[ ]<br>GROUND-2271285-[ ]  | MICRO MOTOR CONN.                                    | 114-5377         |                            |
|  | 0.51-0.53 [20]  |  |  | 1   |   | RECPT.                         |  |   |  |                  | 1.00 ± 0.05 [.0394 ± .002] |
|  | 0.34-0.37 [22]  |  |  | 2   |   | PIN                            |  |   |  |                  | 0.85 ± 0.05 [.0335 ± .002] |
| 2217746-1  | 0.50-1.40 [2X20-2X18-16]  | 4.06 MAX [.160 MAX]  | NO   | NO  | 3.56 ± 0.38 [.140 ±.015]  | 1.384 ± 0.051 [.0545 ±.0020]   | 42840-3<br>66028-3<br>[ ]-583989-[ ]<br>583991-3   | 42717-3<br>[ ]-583361-[ ]<br>60151-[ ]<br>42840-1<br>1-42840-3<br>1-42840-4                       | 60082-1<br>1-60082-3<br>66028-1<br>1-66028-3         | AMP LEAF CONTACT | 114-9003                   |
|  | 0.50-0.60 [20]  | 1.40-2.03 [.055-.080]  |  |   |   | 1.054 ± 0.038 [.0415 ±.0015]   |  |   |  |                  |                            |
| 2217743-1  | 0.40-1.00 [21-8/2X22]   | 3.05 MAX [.120 MAX]  | NO   | NO  | 3.56 ± 0.38 [.140 ±.015]  | 1.029 ± 0.038 [.0405 ±.0015]   | 42840-3<br>583268-[ ]  | 42717-1<br>42702-1<br>583267-[ ]<br>583271-[ ]  | 583272-[ ]<br>583990-[ ]<br>583991-[ ]<br>583989-[ ] | AMP LEAF CONTACT | 114-9003                   |
|  | 0.10-0.40 [26-22]   | 1.27-1.53 [.050-.060]  |  |   |   | 0.775 ± .0038 [.0305 ±.0015]   |  |   |  |                  |                            |


 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

 -1 IS A CERTI-CRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTI-CRIMP II HEAD SUB-ASSEMBLY.

4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414. THE 91538-1 AND -3 TOOL USE IS 408-10274.










2. AMP, CERTI-CRIMP & AMP-BLADE ARE TRADEMARKS.

## CERTI-CRIMP II DATA SHEET


|                           |  |                            |  |   |  |
|---------------------------|--|----------------------------|--|---|--|
| DWG: M. YOUNGER 21FEB2012 |  | MATERIAL: -                |  | HEAT TREAT: -   |  |
| CHK: B.A. WOLFE 22FEB2012 |  | APVD: B.A. WOLFE 22FEB2012 |  |  TE Connectivity |  |
| NAME: B.A. WOLFE          |  | DRAWING NO: 1583011        |  |   |  |
| SCALE: -                  |  | SIZE: A1                   |  | SHEET: 7 of 8   |  |
| REV: F15                  |  | DATE: -                    |  | DATE: -   |  |

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS THE PROPERTY OF TE CONNECTIVITY AND IS NOT TO BE DISCLOSED, REPRODUCED, COPIED, OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, WITHOUT AUTHORIZATION FROM TE CONNECTIVITY.

THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO. 1583011

| TOOL NUMBER<br> | WIRE SIZE<br>mm <sup>2</sup> [AWG]<br> | INSULATION DIAMETER<br>mm [in.]<br> | INSUL. ADJ.<br> | FLIP LOCATOR<br> | STRIP LENGTH<br>mm [in.]<br> | CRIMP HEIGHT<br>mm [in.]        | CONTACT PART NUMBERS  |   | CONTACT DESCRIP.             | APPLIC. SPECIF. |
|--|---|--|--|---|---|---------------------------------|--|---|------------------------------|-----------------|
|  |   |  |  |   |   |                                 | LOOSE PIECE<br>       | STRIP FORM<br> |                              |                 |
| 2217763-1  | 0.30-0.60<br>(22-20)  | 1.02-2.04<br>(.040-.080)   | NO   | NO  | 3.3 ± 0.4<br>(.130 ± .015)  | 1.067 ± 0.038<br>(.042 ± .0015) | 66010-2  | 66005   | AMP BLADE RECEPT.            | 108-9201        |
|  | 0.12-0.20<br>(26-24)  | 1.02-1.53<br>(.040-.060)   |  |   |   | 0.813 ± 0.038<br>(.032 ± .0015) | 66011-2  | 66009   |                              |                 |
| 2217748-1  | 0.80-0.50<br>[18-20]  | 1.7-2.7<br>[.067-.106]   | YES  | NO  | 5.10 ± 0.40<br>[.200 ± .016]  | 1.22 ± 0.05<br>[.048 ± .002]    | 770854-1   | 770520-1  | AMPSEAL                      | 114-16016       |
|  | 1.40<br>[16]  |  |  |   |   | 1.40 ± 0.05<br>[.055 ± .002]    |  |   |                              |                 |
| 2217753-1  | 1.4-2.1<br>[16-14]  | 2.26-3.18<br>[.089-.125]   | NO   | NO  | 5.08 ± 0.40<br>[.200 ± .016]  | 1.55 ± 0.05<br>[.061 ± .002]    | -  | 776491-[ ]  | HDSF SIZE 16<br>PIN & SOCKET | 114-13045       |
|  | 0.90<br>[18]  |  |  |   |   | 1.37 ± 0.05<br>[.054 ± .002]    |  | 638112-[ ]  |                              |                 |
| 2844375-1  | 0.13<br>[26]  | 0.85-1.05<br>[.033-.041]   | NO   | YES   | 3.25-3.55<br>[.128-.140]  | 0.59 ± 0.02<br>[.0230 ± .0008]  | -  | 2098583-4   | 0.50MM RECEPTICLE<br>CONTACT | 114-13287       |
|  | 0.35<br>[22]  | 1.10-1.20<br>[.043-.047]   |  |   |   | 0.67 ± 0.03<br>[.0264 ± .0012]  | -  | 2098583-1   |                              |                 |
|  | 0.35<br>[22]  | 1.10-1.40<br>[.043-.055]   |  |   |   | 0.68 ± 0.02<br>[.0268 ± .0008]  | -  | 2098583-2   |                              |                 |

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY. IT IS THE PROPERTY OF TE CONNECTIVITY AND IS NOT TO BE DISCLOSED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN AUTHORIZATION FROM TE CONNECTIVITY.

|               |  |                 |      |     |      |                   |  |  |  |                     |  |              |  |                 |  |
|---------------|--|-----------------|------|-----|------|-------------------|--|--|--|---------------------|--|--------------|--|-----------------|--|
| P LTR         |  | REVISION RECORD | DATE | DWN | APVD | DIMENSIONS:<br>mm |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:   |  | DRAWING NO. 1583011 |  | SHEET 8 OF 8 |  | REV F15         |  |
| - SEE SHEET 1 |  |                 |      |     |      | 0 PLC ± -         |  | 1 PLC ± -  |  | 2 PLC ± -           |  | 3 PLC ± -    |  | 4 PLC ± -       |  |
| -             |  |                 |      |     |      | ANGLES: -         |  | SURFACE TEXTURE:  |  | SCALE: -            |  | SIZE: A1     |  | TE Connectivity |  |

|      |            |           |          |   |            |   |
|------|------------|-----------|----------|---|------------|---|
| DWN  | M. YOUNGER | 21FEB2012 | MATERIAL | - | HEAT TREAT | - |
| CHK  | B.A. WOLFE | 22FEB2012 |          |   |            |   |
| APVD | B.A. WOLFE | 22FEB2012 |          |   |            |   |



CERTI-CRIMP II TOOL DATA SHEET  
MISCELLANEOUS CONTACTS