

LED inspection lamp

With flexible shaft and 2 surface-mounted mirrors

ORION[®]

Application:

For lighting and inspecting partly concealed areas.

Version:

- Flexible shaft, 8 mm in diameter
- Head part: 10.5 mm

Delivery:

Lamp with shaft, ring magnet, round mirror 30 mm, rectangular mirror 65 x 43 mm, 2 x LR03 AAA batteries



Art. no.	52995 300
Width of mirror	43 mm
Mirror height	65 mm
Max. extension length	600 mm

EAN-Code

4039247877751