

TEGERA® 297

Leather glove, winter-lined, 0,7-0,8 mm full grain goatskin, neoprene, spandex, Thinsulate™ 100g, Cat. II, blue, black, white, reinforced fingers and thumb, waterproof, Velcro®, for allround work

PROPERTIES

High level of protection, good fingertip sensitivity, extra flexible, durable, good grip, perfect fit, extra comfortable, warm

SPECIFICATION

TYPE OF GLOVE Cold insulation gloves

CATEGORY Cat. II

SIZE RANGE (EU) 8, 9, 10, 11

PALM MATERIAL Full grain goatskin

PALM THICKNESS 0,7-0,8 mm

BACK MATERIAL Neoprene, Spandex

LINING Winter-lined

LINING MATERIAL Thinsulate™ 100g

CLO LINING 1,3 m²-K/W

DEXTERITY 5

CUFF MATERIAL Textile

FASTENING Velcro®

COLOUR Blue, black, white

PAIRS PER PACKAGE/CARTON 6/60

DISPLAY Hook with hangtag

OUTER MATERIAL SPECIFICATION Leather, elastane, polyester, natural latex

MIDDLE MATERIAL SPECIFICATION Polyethylene

INNER MATERIAL SPECIFICATION Polyester



AQUATHAN®



Thinsulate
INSULATION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

TEGERA® 297

FEATURES

Reinforced fingers and thumb, pre-curved fingers, waterproof, moisture resistant

PRIMARY PROTECTION

Prevents risk of: abrasion injuries, blisters, grazes, scratches, lacerations, contact with moisture, contact with damp, contact with cold

PRIMARY ENVIRONMENTS OF USE

Cold environments, wet environments, moist environments

PRIMARY AREAS OF USE

Machine operating, building and construction, carpentry, HVAC installation, construction, soil preparation, concrete work, transport work, machine driving, warehouse work, airport work, wood industry work, forest work, agricultural work, gardening, repair work, fishing, hunting, decontamination, sanitation

PRIMARY INDUSTRIES OF USE



Automotive, transportation, utilities, building and construction, logistics, facilities, service, retail

TYPE OF WORK

Medium weight



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-03-06

2(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

TEGERA® 297

EC TYPE EXAMINATION

Notified Body: 0075 CTC, 4 rue Hermann Frenkel, 69367 Lyon Cedex 07 France

COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
A) Resistance to abrasion (No. of revolutions)	2	(4)
B) Resistance to cutting (Index)	1	(5)
C) Tear resistance (Newton)	2	(4)
D) Puncturing resistance (Newton)	2	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).

Level of protection/Performance level	1	2	3	4	5
A) Resistance to abrasion (No. of revolutions)	100	500	2 000	8 000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	

EN 511:2006 Protective gloves against cold



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-03-06

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com