





# Water jerrycans PROFI 12 L, HD-PE

natural, with UV protection



## Description:

Water jerrycans PROFI 12 L, natural-coloured made of fracture-proof polyethylene (HD-PE), stackable

- intake integrated in jerrycan for safe, space-saving deposit of spigot and screw plug
- space-saving and stackable
- large opening (48 mm diameter) allows easy filling, emptying and cleaning
- Canister (production date until October 2021!) with screw connection ET-232802 and (from October 2021!) with screw connection ET-232101 including removable drain tap Art.-No. 550105
- with gripping surface on the base for secure handling
- resistant to greases, resins, alkalis, oils and acids
- opening sealed with screw plug for screwing in spigots and corner valves (wide thread 22 mm)
- on request: Custom-made product without screw plug opening, branding, print, labelling, individual scales and colours possible
- food-safe, resistant to temperature: -20°C to +70°C and free from bisphenol A (BPA)
- w = inside diameter of filling opening = 48 mm / a = outside thread diameter = 65 mm
- d=depth=165 mm w=width=350 mm h=height=310 mm

## Information:

### Article

Articlenumber	<b>816500</b>
GTIN	<b>4007228816501</b>
Customs tariff	<b>39233090</b>
Packaging Unit (PU)	<b>5</b>

Colour	<b>natural</b>
Volume in l	<b>12</b>
Weight (kg)	<b>1,02</b>
T x B x H (mm)	<b>165 x 350 x 310</b>

### Outer packaging

Content in pieces	<b>5</b>
L x B x H (mm)	<b>790 x 340 x 355</b>

Gross weight unit (kg)	<b>5,611</b>
------------------------	--------------

### Pallet

Number of boxes	<b>18</b>
Number of layers	<b>6</b>
L x B x H (m)	<b>1,2 x 0,8 x 2,28</b>

Carton per layer	<b>3</b>
Weight (kg)	<b>120,998</b>