

### Product type designation

Product description

### Cable RS422, Sub-D / M12

Highly flexible communication line (6-core)  
SIMATIC RF, MV CONNECT. CABLE, PREASSEMBLED,  
BETWEEN RF120C AND READER PUR, CMG, TRAILING,  
LENGTH 10 M



Suitability for use	Plug-in cable for connecting a reader to the RF120C communication module
Cable designation	L-YC11Y 6x1x0.25 6x24AWG CMG
Cable length	10 m

### Electrical data

Number of electrical connections	2
Type of electrical connection	Sub-D (male, 9 pin, 45°) / M12 (female, 8 pin, straight)
Loop resistance per length / maximum	160 mΩ/m
Insulation resistance coefficient	20 GΩ·m
Operating voltage	
• maximum	300 V

### Mechanical data

Number of electrical cores	6
Design of the shield	Braided shield made of tin-plated copper wires
Outer diameter	
• of cable sheath	5.4 mm
Symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
Material	
• of the wire insulation	PVC
• of cable sheath	PUR
Color	
• of the insulation of data wires	DIN 47100

• of cable sheath	Black
Bending radius	
• with single bend / minimum permissible	21.6 mm
• with multiple bends / minimum permissible	43 mm
• with continuous bending	75 mm
Number of bending cycles	3000000
Tensile load / maximum	200 N
Weight per length	45 kg/km

#### Permitted ambient conditions

Ambient temperature	
• during operation	-30 ... +80 °C
• during storage	-30 ... +80 °C
• during transport	-30 ... +80 °C
• during installation	-30 ... +80 °C
Burning behavior	flame resistant according to IEC 60332-1-2
Chemical resistance	
• to mineral oil	resistant
• to grease	Resistant
Radiological resistance / to UV radiation	resistant

#### Product properties, functions, components / general

Product property	
• halogen-free	No
• silicon-free	Yes

#### Further Information / Internet Links

Internet-Link	
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAx Download Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**last modified:** 16.03.2015