

## Tap wrench Basic

For holding square-head screw taps and reamers in accordance with DIN 10

**ORION**<sup>®</sup>

### Application:

For holding square-head screw taps in accordance with DIN 10, reamers, screw extractors, screw tap extensions, tools with square mounts

### Version:

- Housing, size 0-5, made of die-cast zinc, zinc-plated arm with knurling for medium loads

### Advantage:

- Die-cast zinc ensures excellent value for money
- Ground and hardened steel jaws



<b>Art. no.</b>	<b>13549 005</b>
<b>Tap wrench size</b>	0
<b>Suitable for min./max. square socket size</b>	2-5 mm
<b>Min./max. reamer cutting range</b>	2.5-6.5 mm
<b>Min./max. thread-cutting area, metric</b>	1-8 mm
<b>Length</b>	125 mm

### EAN-Code

4039247076635