

3-sided shelf trolley with 5 load areas, load capacity 600 kg

Height 1800 mm, 3 load area sizes

fetra
Transportgeräte

Application:

For transporting non-stacking goods and materials, for continuous use in industrial applications.

Version:

- Modular system, can be completely fixed with screws
- Steel tube/profile steel welded
- Front walls with vertical tube struts (distance approx. 130 mm)
- 1 fixed load area
- Rigid sandwich panels

Advantage:

- Robust design and high load capacity ensure a long service life even when used for high industrial loads
- Multiple load areas provide ample storage space for non-stacking goods and crates
- FETRA plug-and-screw design allows trolleys and accessories to be altered easily
- Large high-quality rollers for good running properties
- Vertical tubular struts prevent parts falling forwards and backwards

Delivery:

Disassembled



Art. no.	50268 295
Load-carrying capacity	600 kg
Load-carrying capacity of loading surfaces	90 kg
Number of loading surfaces	5
Loading surface size	1000 x 800 mm
Loading-surface width	800 mm
Loading-surface height	269 mm
Loading-surface height 2	569 mm
Loading-surface height 3	869 mm
Loading-surface height 4	1169 mm
Loading-surface height 5	1469 mm
Loading surface length	1000 mm
Length	1369 mm
Width	830 mm
Height	1800 mm
Number of fixed rollers	2
Length x width x height	1369 x 830 x 1800 mm
Number of steering rollers	2
With wheel lock	Yes
Total stop optional	Yes
Wheel width	40 mm
Wheel diameter	200 mm
Material of wheel	TPE

EAN-Code

4017976835310