

Collet chucks type ER25 in accordance with DIN 6499 A

HP = high precision, concentricity < 5 µm

ATORN[®]

Application

For use on precision collet chucks

Advantage

- Higher concentricity extends tool life

Art. No.	23388 021
Collet type	ER 25
Clamping diameter	1 mm
Min./max. clamping range	1-16 mm
Outer diameter	26 mm
Length	34 mm
Clamping bypass	-0.5 mm



EAN-Code

4050293629910