

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Everbuild 125 One Hour Caulk

1.2 Relevant identified uses of the substance or mixture and uses advised against

Product use : Sealant/adhesive

1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company
Site 41
Knowsthorpe Way
Cross Green Industrial Estate
Leeds
West Yorkshire LS9 0SW
United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Reproductive toxicity, Category 2 H361d: Suspected of damaging the unborn child.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Warning

Hazard statements : H361d Suspected of damaging the unborn child.

Precautionary statements : **Prevention:**

P201 Obtain special instructions before use.
P202 Do not handle until all safety precautions

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



P280	have been read and understood. Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response:	
P308 + P313	IF exposed or concerned: Get medical ad- vice/ attention.
Storage:	
P405	Store locked up.
Disposal:	
P501	Dispose of contents/container in accordance with local regulation.

Hazardous components which must be listed on the label:

- 1-isopropyl-2,2-dimethyltrimethylene diisobutyrate

Additional Labelling

EUH208 Contains mixture of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1) (C(M)IT/MIT (3:1)).
May produce an allergic reaction.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Registration number	Classification	Concentration (% w/w)
1-isopropyl-2,2-dimethyltrimethylene diisobutyrate	6846-50-0 229-934-9 01-2119451093-47-XXXX	Repr. 2; H361d Aquatic Chronic 3; H412	>= 5 - < 10
mixture of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1) (C(M)IT/MIT (3:1))	55965-84-9 Not Assigned 01-2120764691-48-XXXX	Acute Tox. 3; H331 Acute Tox. 2; H310 Acute Tox. 3; H301 Skin Corr. 1B; H314 Skin Sens. 1A; H317 Aquatic Acute 1; H400 Aquatic Chronic 1; H410	>= 0,0002 - < 0,0015

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



SECTION 4: First aid measures

4.1 Description of first aid measures

- General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.
- If inhaled : Move to fresh air.
Consult a physician after significant exposure.
- In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.
- In case of eye contact : Remove contact lenses.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

- Symptoms : See Section 11 for more detailed information on health effects and symptoms.
- Risks : No known significant effects or hazards.
Suspected of damaging the unborn child.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media : In case of fire, use water/water spray/water jet/carbon dioxide/sand/foam/alcohol resistant foam/chemical powder for extinction.

5.2 Special hazards arising from the substance or mixture

- Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
- Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Deny access to unprotected persons.

6.2 Environmental precautions

Environmental precautions : Try to prevent the material from entering drains or water courses.
No special environmental precautions required.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see section 8).
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Store in original container. Keep container tightly closed in a dry and well-ventilated place. Observe label precautions.
Store in accordance with local regulations.

Further information on storage stability : No decomposition if stored and applied as directed.



7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Personal protective equipment

- Eye protection : Safety glasses with side-shields conforming to EN166
Eye wash bottle with pure water
- Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.
- Suitable for short time use or protection against splashes:
Butyl rubber/nitrile rubber gloves (0,4 mm)
Contaminated gloves should be removed.
Suitable for permanent exposure:
Viton gloves (0.4 mm),
breakthrough time >30 min.
- Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.
- Respiratory protection : No special measures required.

Environmental exposure controls

- General advice : Try to prevent the material from entering drains or water courses.
No special environmental precautions required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

- Appearance : paste
- Colour : various
- Odour : No data available
- Odour Threshold : No data available
- pH : 8,5 - 9,5

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



Melting point/range / Freezing point	:	No data available
Boiling point/boiling range	:	No data available
Flash point	:	> 61 °C
Evaporation rate	:	No data available
Flammability (solid, gas)	:	No data available
Upper explosion limit / Upper flammability limit	:	No data available
Lower explosion limit / Lower flammability limit	:	No data available
Vapour pressure	:	23 hPa
Relative vapour density	:	No data available
Density	:	1,65 g/cm ³
Solubility(ies)		
Water solubility	:	soluble
Solubility in other solvents	:	No data available
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity		
Viscosity, dynamic	:	No data available
Viscosity, kinematic	:	> 20,5 mm ² /s (40 °C)
Explosive properties	:	No data available
Oxidizing properties	:	No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.



10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : No hazards to be specially mentioned.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

No decomposition if stored and applied as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Components:

1-isopropyl-2,2-dimethyltrimethylene diisobutyrate:

Acute oral toxicity : LD50 Oral (Rat): > 3.200 mg/kg

Acute dermal toxicity : LD50 Dermal (Rat): > 5.000 mg/kg

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Suspected of damaging the unborn child.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

Components:

mixture of: 5-chloro-2-methyl-4-isothiazolin-3-one [EC no. 247-500-7] and 2-methyl-2H-isothiazol-3-one [EC no. 220-239-6] (3:1) (C(M)IT/MIT (3:1));

M-Factor (Acute aquatic toxicity) : 100

M-Factor (Chronic aquatic toxicity) : 10

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

12.6 Other adverse effects

Product:

Additional ecological information : There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated by dangerous substances

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

International Chemical Weapons Convention (CWC) : Not applicable
Schedules of Toxic Chemicals and Precursors

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed (=> 0.1 %).

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



- Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable
- Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable
- REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Conditions of restriction for the following entries should be considered: Number on list 3
- REACH Information: All substances contained in our Products are
- registered by our upstream suppliers, and/or
- registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

- Volatile organic compounds : Law on the incentive tax for volatile organic compounds (VOCV)
no VOC duties
- Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

- Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations
Health and Safety at Work Act 1974 & Subsidiary Regulations
Control of Substances Hazardous to Health Regulations (COSHH)
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this mixture by the supplier.

SECTION 16: Other information

Full text of H-Statements

- H301 : Toxic if swallowed.
H310 : Fatal in contact with skin.
H314 : Causes severe skin burns and eye damage.
H317 : May cause an allergic skin reaction.
H331 : Toxic if inhaled.
H361d : Suspected of damaging the unborn child.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild 125 One Hour Caulk

Revision Date 13.05.2019

Version 7.0

Print Date 13.05.2019



BUILDING TRUST



- H400 : Very toxic to aquatic life.
- H410 : Very toxic to aquatic life with long lasting effects.
- H412 : Harmful to aquatic life with long lasting effects.

Full text of other abbreviations

- Acute Tox. : Acute toxicity
- Aquatic Acute : Short-term (acute) aquatic hazard
- Aquatic Chronic : Long-term (chronic) aquatic hazard
- Repr. : Reproductive toxicity
- Skin Corr. : Skin corrosion
- Skin Sens. : Skin sensitisation
- ADR : European Agreement concerning the International Carriage of Dangerous Goods by Road
- CAS : Chemical Abstracts Service
- DNEL : Derived no-effect level
- EC50 : Half maximal effective concentration
- GHS : Globally Harmonized System
- IATA : International Air Transport Association
- IMDG : International Maritime Code for Dangerous Goods
- LD50 : Median lethal dose (the amount of a material, given all at once, which causes the death of 50% (one half) of a group of test animals)
- LC50 : Median lethal concentration (concentrations of the chemical in air that kills 50% of the test animals during the observation period)
- MARPOL : International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
- OEL : Occupational Exposure Limit
- PBT : Persistent, bioaccumulative and toxic
- PNEC : Predicted no effect concentration
- REACH : Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
- SVHC : Substances of Very High Concern
- vPvB : Very persistent and very bioaccumulative

Further information

Classification of the mixture:

|| Repr. 2 H361d

Classification procedure:

Calculation method

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

|| Changes as compared to previous version !

GB / EN



BUILDING TRUST

