

RES.CUR.OP.CIRCUIT BREAKER TYPE A 25A 3+N-  
POLE 30MA 400V 4MW N-LEFT



Figure similar

Model		
product brand name		SENTRON
Product designation		RCCB
<b>Design of the product</b>		Instantaneous
<b>Product variations</b>		N left
General technical data		
<b>Number of poles</b>		4
<b>Size of installation devices / acc. to DIN 43880</b>		1
<b>Protection against electrical shock</b>		Finger and back-of-hand safe
<b>Short-circuit current rating</b>	kA	10
<b>circuit-breaker / Design</b>		5SV3
<b>Mechanical service life (switching cycles) / typical</b>		10 000
<b>Overvoltage category</b>		III
Protection class		
<b>Protection class IP</b>		IP20, if the distribution board is installed, with connected conductors
Switching capacity		
<b>Switching capacity current</b>		
<ul style="list-style-type: none"> <li>acc. to EN 60898 / Rated value</li> </ul>	kA	0.8
Dissipation		
<b>Active power loss</b>		
<ul style="list-style-type: none"> <li>for rated value of the current / with AC / in hot operating state / per pole</li> </ul>	W	3.9

Electricity		
<b>Tripping residual current / Rated value</b>	mA	30
rated current $I_n$ / IEC, DIN/VDE / at 40 Cel	A	25
Current / with AC / Rated value	A	25
Surge current resistance / Rated value	kA	1

Product details		
<b>Product property</b>		
<ul style="list-style-type: none"> <li>• halogen-free</li> </ul>		Yes
<ul style="list-style-type: none"> <li>• silicon-free</li> </ul>		Yes
Product expansion / can be installed / supplementary devices		Yes

Number		
<b>Number of test cycles / for environmental testing / acc. to IEC 60068-2-30</b>		28

Connections		
<b>Connectable conductor cross-section / stranded</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	mm <sup>2</sup>	0.75
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	mm <sup>2</sup>	35
<b>Connectable conductor cross-section / solid</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	mm <sup>2</sup>	0.75
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	mm <sup>2</sup>	35
<b>Tightening torque / with screw-type terminals</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	N·m	2.5
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	N·m	3
Position / of power supply cord		top or bottom

Mechanical Design		
<b>Height</b>	mm	90
<b>Width</b>	mm	72
<b>Depth</b>	mm	70
<b>mounting position</b>		any
<b>Installation depth</b>	mm	70
<b>Number of width units</b>		4
<b>Mounting type</b>		DIN rail (REG)

Environmental conditions		
<b>Ambient temperature</b>		
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	°C	-25
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	°C	45
<ul style="list-style-type: none"> <li>• during storage / minimum permissible</li> </ul>	°C	-40
<ul style="list-style-type: none"> <li>• during storage / maximum permissible</li> </ul>	°C	75

Certificates		
--------------	--	--

**Equipment marking**

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F  
F

**General Product Approval**

**Declaration of Conformity**



ÖVE



GOST



other



EG-Konf.

**Further information**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SV33426KL>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/5SV33426KL/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SV33426KL](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SV33426KL)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>



Siemens

5SV(3,4)x4x-x

Format / Size: Hybrid quer

last modified:

11.03.2015