

Safety Data Sheet

according to Regulation (EC) No. 453/2010

Revision date : 4.9.17

Supercedes : 08/11/2016

Revision:2

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
 Product name : PRIVATE LABEL POT POURRI AIR FRESHENER
 Part no : PLB1005 / PLB/SPD1042
 Type of product : Aerosol
 Vaporizer : Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
 Industrial/Professional use spec : For professional use only
 Use of the substance/mixture : air freshener

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

STAPLES CHEMICALS
 Neville House
 Beaumont Rd
 Banbury, Oxon
 OX16 1RB
 Tel: +44 (0) 1295 251721
 FAX: +44 (0) 1295 269561
 E Mail: sales@cleenol.co.uk

1.4. Emergency telephone number

Emergency contact number 01295 251721 (9am to 5pm Monday to Friday excluding bank holidays). Ask for Technical Department quoting the product name. Outside of these hours please contact your doctor or local hospital accident and emergency department or the NHS enquiry service (dial 111) quoting product name and present this MSDS advising them that the product is registered with the National Poisons Information Service.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture


Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol 1 H222;H229

Full text of H-phrases: see section 16

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) : 

GHS02

Signal word (CLP) : Danger
 Hazard statements (CLP) : H222 - Extremely flammable aerosol
 H229 - Pressurised container: May burst if heated

Precautionary statements (CLP) : P102 - Keep out of reach of children
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
 P211 - Do not spray on an open flame or other ignition source
 P251 - Do not pierce or burn, even after use
 P273 - Avoid release to the environment
 P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substance

Not applicable

Safety Data Sheet

3.2. Mixture

Name	Product identifier	%	Classification according to Regulation EC No. 1272/2008 [CLP]
propane substance with national workplace exposure limit(s) (DK, IE)	(CAS No) 74-98-6 (EC no) 200-827-9 (EC index no) 601-003-00-5	5 - 15	Flam. Gas 1, H220
butane substance with national workplace exposure limit(s) (DK, GB, IE)	(CAS No) 106-97-8 (EC no) 203-448-7 (EC index no) 601-004-00-0	5 - 15	Flam. Gas 1, H220 Press. Gas
propan-2-ol, isopropyl alcohol, isopropanol	(CAS No) 67-63-0 (EC no) 200-661-7 (EC index no) 603-117-00-0 (REACH-no) 01-2119457558-25	1 - 5	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336

Full text of R- and H-phrases: see section 16

SECTION 4: First aid measures**4.1. Description of first aid measures**

First-aid measures general	: Get medical advice/attention if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash with plenty of soap and water.
First-aid measures after eye contact	: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Do NOT induce vomiting. Rinse mouth. Drink plenty of water. Get medical advice/attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries	: Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/injuries after inhalation	: May cause respiratory irritation.
Symptoms/injuries after skin contact	: Repeated exposure may cause skin dryness or cracking.
Symptoms/injuries after eye contact	: Causes eye irritation.
Symptoms/injuries after ingestion	: May cause a light irritation of the linings of the mouth, throat, and gastrointestinal tract.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures**5.1. Extinguishing media**

Suitable extinguishing media : Carbon dioxide. Dry powder. Foam.

5.2. Special hazards arising from the substance or mixture

Fire hazard	: Extremely flammable aerosol.
Explosion hazard	: Explosion risk in case of fire.

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

General measures : Remove ignition sources.

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Use personal protective equipment as required.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment	: Collect spillage.
Methods for cleaning up	: Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For further information refer to section 13.

Safety Data Sheet

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Additional hazards when processed	: Pressurized container: Do not pierce or burn, even after use.
Precautions for safe handling	: Do not spray on an open flame or other ignition source.
Hygiene measures	: Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures	: Does not require any specific or particular technical measures.
Storage conditions	: Keep away from ignition sources. Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
Incompatible products	: Oxidizing agent. Strong acids. Strong bases.
Incompatible materials	: Direct sunlight. Heat sources. Sources of ignition.
Special rules on packaging	: Keep only in original container.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection**8.1. Control parameters**

propane (74-98-6)		
Denmark	Local name	Propan
Denmark	Grænseværdie (langvarig) (mg/m ³)	1800 mg/m ³
Denmark	Grænseværdie (langvarig) (ppm)	1000 ppm
Ireland	Local name	Propane
Ireland	OEL (8 hours ref) (ppm)	1000 ppm
Ireland	Notes (IE)	Asphx
propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)		
Denmark	Local name	Isopropylalkohol (2005)
Denmark	Grænseværdie (langvarig) (mg/m ³)	490 mg/m ³
Denmark	Grænseværdie (langvarig) (ppm)	200 ppm
Germany	TRGS 900 Limitation of exposure peaks (mg/m ³)	1000 mg/m ³
Ireland	Local name	Isopropyl alcohol
Ireland	OEL (8 hours ref) (ppm)	200 ppm
Ireland	OEL (15 min ref) (ppm)	400 ppm
Ireland	Notes (IE)	Sk
Netherlands	Grenswaarde TGG 8H (mg/m ³)	650 mg/m ³
Netherlands	Grenswaarde TGG 15MIN (mg/m ³)	0 mg/m ³
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m ³)	999 mg/m ³
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m ³)	1250 mg/m ³
United Kingdom	WEL STEL (ppm)	500 ppm
butane (106-97-8)		
Denmark	Local name	n-Butan
Denmark	Grænseværdie (langvarig) (mg/m ³)	1200 mg/m ³
Denmark	Grænseværdie (langvarig) (ppm)	500 ppm
Ireland	Local name	Butane
Ireland	OEL (8 hours ref) (ppm)	1000 ppm
United Kingdom	Local name	Butane
United Kingdom	WEL TWA (mg/m ³)	1450 mg/m ³
United Kingdom	WEL TWA (ppm)	600 ppm
United Kingdom	WEL STEL (mg/m ³)	1810 mg/m ³
United Kingdom	WEL STEL (ppm)	750 ppm
United Kingdom	Remark (WEL)	Carc, (only applies if Butane contains more than 0.1% of buta-1,3-diene)

Safety Data Sheet

8.2. Exposure controls

Materials for protective clothing	: Not required for normal conditions of use
Hand protection	: In case of repeated or prolonged contact wear gloves
Eye protection	: Not required for normal conditions of use
Skin and body protection	: Not required for normal conditions of use
Respiratory protection	: Not required for normal conditions of use

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Aerosol.
Colour	: Colourless.
Odour	: Floral
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: No data available
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 0.81
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Pressurised container: May burst if heated.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No additional information available

10.4. Conditions to avoid

Direct sunlight. Heat. Open flame.

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

No additional information available

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	: Not classified
Skin corrosion/irritation	: Not classified

Safety Data Sheet

Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
Specific target organ toxicity (single exposure)	: Not classified
Specific target organ toxicity (repeated exposure)	: Not classified
Aspiration hazard	: Not classified

AIRFRESHENER -

Vaporizer	Aerosol
-----------	---------

SECTION 12: Ecological information

12.1. Toxicity

propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)

LC50 fishes 1	9640 mg/l
EC50 other aquatic organisms 1	13299 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	> 1000 mg/l IC50 algea (72 h) mg/l

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)

Log Pow	0.14
---------	------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste disposal recommendations : Do not pierce or burn, even after use.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

14.1. UN number

UN-No. (ADR)	: 1950
UN-No. (IMDG)	: 1950
UN-No.(IATA)	: 1950

14.2. UN proper shipping name

Proper Shipping Name (ADR)	: AEROSOLS
Proper Shipping Name (IMDG)	: AEROSOLS
Proper Shipping Name (IATA)	: AEROSOLS, FLAMMABLE
Transport document description (ADR)	: UN 1950 AEROSOLS, 2.1, (D)
Transport document description (IMDG)	: UN 1950 AEROSOLS, 2.1

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR)	: 2.1
Danger labels (ADR)	: 2.1



Safety Data Sheet

IMDG

Transport hazard class(es) (IMDG) : 2.1
 Danger labels (IMDG) : 2.1



IATA

Transport hazard class(es) (IATA) : 2.1
 Hazard labels (IATA) : 2.1



14.4. Packing group

Packing group (ADR) : Not applicable
 Packing group (IMDG) : Not applicable
 Packing group (IATA) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No
 Marine pollutant : No
 Other information : No supplementary information available

14.6. Special precautions for user

- Overland transport

Classification code (ADR) : 5F
 Special provisions (ADR) : 190, 327, 344, 625
 Limited quantities (ADR) : 1L
 Excepted quantities (ADR) : E0
 Packing instructions (ADR) : P207, LP02
 Special packing provisions (ADR) : PP87, RR6, L2
 Mixed packing provisions (ADR) : MP9
 Transport category (ADR) : 2
 Special provisions for carriage - Packages (ADR) : V14
 Special provisions for carriage - Loading, unloading and handling (ADR) : CV9, CV12
 Special provisions for carriage - Operation (ADR) : S2
 Tunnel restriction code (ADR) : D

- Transport by sea

Special provisions (IMDG) : 63, 190, 277, 327, 344, 959
 Limited quantities (IMDG) : SP277
 Excepted quantities (IMDG) : E0
 Packing instructions (IMDG) : P207, LP02
 Special packing provisions (IMDG) : PP87, L2
 EmS-No. (Fire) : F-D
 EmS-No. (Spillage) : S-U
 Stowage category (IMDG) : None

Safety Data Sheet

- Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg
CAO packing instructions (IATA)	: 203
CAO max net quantity (IATA)	: 150kg
Special provisions (IATA)	: A145, A167, A802
ERG code (IATA)	: 10L

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

IBC code : Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no substances with Annex XVII restrictions
 Contains no substance on the REACH candidate list
 Contains no REACH Annex XIV substances

15.1.2. National regulations

Germany

VwVwS Annex reference : Water hazard class (WGK) 2, hazardous to water (Classification according to VwVwS, Annex 4)
 12th Ordinance Implementing the Federal Immission Control Act - 12.BImSchV : Is not subject of the 12. BImSchV (Hazardous Incident Ordinance)

Denmark

Recommendations Danish Regulation : Young people below the age of 18 years are not allowed to use the product

15.2. Chemical safety assessment

No additional information available

SECTION 16: Other information

Full text of R-, H- and EUH-phrases:

Aerosol 1	Aerosol, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Gas 1	Flammable gases, Category 1
Flam. Liq. 2	Flammable liquids, Category 2
Press. Gas	Gases under pressure
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H220	Extremely flammable gas
H222	Extremely flammable aerosol
H225	Highly flammable liquid and vapour
H229	Pressurised container: May burst if heated
H319	Causes serious eye irritation
H336	May cause drowsiness or dizziness

SDS EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product