

# Coventry™ Swabs and Wipes

## Coventry™ Sealed Polyester Swabs

Exceptionally clean, tough and durable swabs

An exceptionally clean swab produced by Coventry's proprietary process of forming and welding the swab head without the use of adhesives. Featuring either knit or nonwoven fabric heads, these swabs are acid and solvent resistant. Sealed edges build in high strength with no loose fibers or particulates. Coventry sealed polyester swabs have the strongest seams available and will not split. They are ideal for tough scrubbing around raised shapes. Class 10 (ISO Class 4) processing gives you low ionic, nonvolatile residue and particle contaminants.

36061I cleaned with Aqua-Prime™ process.



**Aqua-Prime** available for special cleaning validation demands. Call 1-800-TECH-401 for details.



Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
36060	500 swabs	5.8" 14.7 cm	0.12" 3.1 mm	0.75" 18.9 mm	0.19" x 0.21" 4.7 mm x 5.4 mm	polypropylene	knit polyester
 For extra cleanliness							
36061I	25 swabs	5.8" 14.7 cm	0.12" 3.1 mm	0.75" 18.9 mm	0.19" x 0.21" 4.7 mm x 5.4 mm	polypropylene	knit polyester
							
36850	500 swabs	5.8" 14.7 cm	0.12" 3.1 mm	0.75" 18.9 mm	0.19" x 0.21" 4.7 mm x 5.4 mm	polypropylene	knit poly/nylon microfiber
							
34860*	500 swabs	2.8" 7.1 cm	0.09" 2.3 mm	0.47" 11.9 mm	0.10" x 0.10" 2.6 mm x 2.6 mm	polypropylene	knit poly/nylon microfiber
 <i>Conical Fabric Swab, 34860, is patented, U.S. Patent number 6629329.</i>							
38040	500 swabs	2.7" 6.9 cm	0.09" 2.3 mm	0.44" 11.2 mm	0.09" x 0.12" 2.4 mm x 3.0 mm	polypropylene flexible tip	knit polyester
							
38140	500 swabs	2.7" 6.9 cm	0.09" 2.3 mm	0.48" 12.1 mm	0.06" x 0.12" 1.6 mm x 3.0 mm	polypropylene flexible tip	knit polyester
							
38540	500 swabs	2.7" 6.9 cm	0.09" 2.3 mm	0.46" 11.7 mm	0.04" x 0.12" 1.0 mm x 3.0 mm	polypropylene flexible tip	nonwoven polyester
							

Pages 66 to 69




A full line of swabs designed specifically for cleaning fiber environments.

## Coventry™ ESD Static Control Swabs

Protects components from destructive static discharge



Engineered to eliminate damage from static electricity. The handles of these swabs will dissipate 99% of a 5,000 volt (5 KV) charge in less than 2.0 seconds. The static dissipative plastic alloy used to make the handles is inherently static dissipative. It contains no additives, coatings or surfactants so it functions at any level of humidity and it is very resistant to solvents — even acetone. Choose between our Class 10 (ISO Class 4) laundered polyester or 100 pore-per-inch ultraclean polyurethane foam.



Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
36060ESD	500 swabs	5.8" 14.7 cm	0.12" 3.1 mm	0.75" 18.9 mm	0.19" x 0.21" 4.7 mm x 5.4 mm	ESD	knit polyester
31040ESD	500 swabs	2.8" 7.2 cm	0.10" 2.7 mm	0.44" 11.0 mm	0.12" x 0.12" 3.1 mm x 3.1 mm	ESD	knit polyester
41050ESD	500 swabs	2.8" 7.2 cm	0.10" 2.6 mm	0.40" 10.2 mm	0.13" x 0.14" 3.3 mm x 3.5 mm	ESD	polyurethane foam
44070ESD	500 swabs	3.2" 8.0 cm	0.10" 2.4 mm	0.39" 9.9 mm	0.11" x 0.13" 2.7 mm x 3.3 mm	ESD	polyurethane foam

