



Untagged 1/2 AA size Lithium Thionyl Chloride cell with a voltage of 3.6V making it suitable for many memory back-up applications.

- Approx dimensions 25 x 14.5mm diameter
- Capacity 850mAh
- Non-rechargeable primary cell
- Typical shelf life: 10 years (approx)
- Date marked on battery is manufacturing date



### Performance Data

(Typical values 25° for batteries stored for one year)

Type	Lithium Thionyl chloride cylindrical cell
Model	1/2 AA
Nominal dimensions (with sleeve)	Ø = 14.7 - 1.2mm H = 25.2 - 1.2mm
Max. continuous discharge current	30mA
Nominal voltage	3.6V
Pulse current capability	60mA
Anode surface area	6cm <sup>2</sup>
Nominal capacity	850mAh
Volume	4.3cm <sup>3</sup>
Weight	10g
Temperature range	-55 to +85°C

**WARNING:** Risk of fire or explosion. Do not recharge, force open, heat, or dispose of in fire.

