


TM-045-BEM18

/US



UL
LISTED

EAC

Measuring range	-40...125 °C	-40...257 °F
Process connection	threaded connection M18 x 1,5 internal thread	
Installation length EL	[mm]	60

Special feature	Gold-plated contacts
Measuring element	1 x Pt 100; (to DIN EN 60751, class B)
Media	liquids and gases
Pressure rating [bar]	300
Minimum installation depth [mm]	15

Protection class	III
------------------	-----

Probe length L	[mm]	44	
Measuring range		-40...125 °C	-40...257 °F

Accuracy	[K]	$\pm (0,30 \text{ K} + 0,005 \times t)$
----------	-----	---

Dynamic response T05 / T09	[s]	1 / 3; (to DIN EN 60751)
----------------------------	-----	--------------------------

Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K

MTTF	[years]	22831
------	---------	-------

TM9950



Temperature sensor with process connection

TM-045-BEM18

/US

Mechanical data

Weight	[g]	81.5
Materials		stainless steel (1.4404 / 316L)
Materials (wetted parts)		stainless steel (1.4404 / 316L)
Process connection		threaded connection M18 x 1,5 internal thread
Probe diameter	[mm]	8.2
Installation length EL	[mm]	60

Remarks

Remarks	operating voltage "supply class 2" according to cULus
	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; Contacts: gold-plated



Connection

