

Brass Blanking Plugs

RoHS
Compliant



Description

Ideal to seal off a hole, when no cable gland is used. It provide a clean finish that can either protect or cover the hole.


Applications

Power (Electrical, Oil and Gas, Wind and Solar)
Railway

Specifications

IP Rating : IP68
Plug Material : Nickel-plated brass
Washer Material : NBR
Working Temperature : -20°C to +80°C

Diagram



Part Number Table

Description	Thread ØD1	H (mm)	GL (mm)	W (mm)	Part Number
Blanking Plug, IP68, Brass	M12×1.5	8	5	14	PELB0232
	M16×1.5	9	6	18	PELB0233
	M20×1.5	9.5	6.5	22	PELB0234
	M25×1.5	11	7	28	PELB0235
	M32×1.5	12	8	35	PELB0236

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.