

Product information

35 22 115

Electronics Pliers

DIN ISO 9655



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Half-round jaws
- Ball bearing chrome steel, oil hardened




General

Article No.	35 22 115
EAN	4003773035114
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 52 x 17 mm
Standard	DIN ISO 9655
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw length (B)	22.5 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	2.0 mm
Tips thickness (F)	1.5 mm
Head width (A)	11.0 mm



technical change and errors excepted

