

FM 100 BT







Safety ensured by Pinch Force Measurement

DriveTest GmbH develops and produces test systems for the worldwide use in the facility management industry. As one of the pioneering companies in the field of pinch force measurement **DriveTest** offers a broad range of different devices for a variety of applications. Every device supports the testing of pinch forces according to an applicable standard. Our customer service comprises the consultation, maintenance and calibration of the measuring devices. Major customers are international airports, building technology companies and facility service companies.

The FM 100 BT from **DriveTest** is a wireless pinch force measuring system for power driven doors and gates. Typical applications include final inspection of new installations, and periodic conformance testing of existing equipment.

The FM 100 BT is a redesign of the proven and tested FM 100. It combines the customer approved rugged

construction and precision of its predecessor with the new flexibility of a wireless solution.

The system is setup for measurements in no time. Connect the device to the app, choose the measurement to perform and the system is ready to test power operated doors according to the applicable standard. The app guides the user through the workflow which is required by the standard. Reports for the performed measurements are instantly generated and are available for sending or storing. The app stores tested doors in a database, thereby facilitates the task of recording periodic measurements. Using barcodes or QR-Codes for identification of tested doors from inside the app is an additional feature preventing errors and making testing even simpler.

- Applicable standards guided workflow and evaluation of EN12453:2017, EN 60335-2, DIN V 18650, ASR A1.7, DHF TS 011:2016 etc.
- Time saver instant feedback and on-site evaluation in combination with digital reports saves a lot of time and will pay off the system within weeks
- Precision measurements uses frictionless guides and single point load cell
- Robust construction casing manufactured from durable material for long service life in industrial environments
- Wireless no more bothersome cables
- Paperless office helps to reduce the time spend with paper work
- Easy to control known principles from everyday life
- Complete customer support in-house calibration service; update service ensures use of newest standards version

Tel.: +49 89 74 34 09 40

Fax: +49 89 74 34 09 49











up to 10 m

FM 100 BT

Sensor FM 100 BT Force Meter App PC-Analysis-Software PinchPilot Measurement Range: 0-2.000 N Intuitive user interface • Graphical display of force vs. time Measurement +/- 3 N or 3 % • Graphical display of force vs. time Calculation of relevant parameters Calculation of relevant parameters Assessment with respect to different Tolerance: whichever is greater Instant feedback for failed/passed Stiffness: 500 N/mm standards • Guided workflow Support for user defined standards Gap width: 50 mm Diameter: 80 mm • Automatic measurement object Printed reports Measurement detection Data export (Excel, CSV, PDF) Technique: Strain Gauge Bridge • Available for Windows Vista, 7, 8 and 10 Instant report creation Size: 210 x 80 x 50 mm • Available for Android 5.0 and newer Connection: USB Weight: Connection: Bluetooth Low Energy 2.1 kg





What's included?

- Wireless force measurement device
- Transportation case with foam inserts for ease of storage and transport
- Android App

Wireless Range:

- USB cable
- User manual
- Calibration certificate
- Various accessories available



