

Welding and inspection mirror with magnetic base

Flexible shaft

ORION[®]

Application:

For checking weld seams in concealed areas.

Version:

- Made from steel, nickel-plated
- With flexible tube
- With permanent adhesive magnet for pipes and straight surfaces

Art. no.	54166 010
Length x width	80 x 70 mm
Length (opened out)	495 mm
Length	80 mm

EAN-Code

4039247307814

