

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Trade name : Glass & Mirror Cleaner  
Product code : CL4006

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use, Consumer use  
Use of the substance/mixture : Cleaning/washing agents and additives  
Function or use category : Cleaning/washing agents and additives

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

##### Supplier

Crown Supplies Ltd  
UNIT 3  
VULCAN ROAD NORTH  
NR6 6AQ Norwich - UK  
T 01603 403 333 - F 01603 403 362  
[sales@crownsupplies.co.uk](mailto:sales@crownsupplies.co.uk) - [www.crownsupplies.co.uk](http://www.crownsupplies.co.uk)

#### 1.4. Emergency telephone number

Emergency number : 01603 403 333  
NORMAL OFFICE HOURS

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

##### Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Signal word (CLP) : No Significant Hazard  
Precautionary statements (CLP) : P102 - Keep out of reach of children.  
Avoid contact with skin and eyes.  
EUH-statements : EUH210 - Safety data sheet available on request.

#### 2.3. Other hazards

No additional information available

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
propan-2-ol; isopropyl alcohol; isopropanol	CAS-No.: 67-63-0 EC-No.: 200-661-7 EC Index-No.: 603-117-00-0 REACH-no: 01-2119457558-25	≥ 0.5 – < 5	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
2-butoxyethanol; ethyleneglycol monobutyl ether; butyl cellosolve	CAS-No.: 111-76-2 EC-No.: 203-905-0 EC Index-No.: 603-014-00-0 REACH-no: 01-2119475108-36	≥ 0.5 – < 5	Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Dermal), H312 Acute Tox. 4 (Inhalation), H332 Acute Tox. 4 (Inhalation:dust,mist), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

No additional information available

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

### 5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area.

#### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 6.2. Environmental precautions

Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material.  
Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### 8.1.1. National occupational exposure and biological limit values

propan-2-ol; isopropyl alcohol; isopropanol (67-63-0)	
United Kingdom - Occupational Exposure Limits	
Local name	Propan-2-ol
WEL TWA (OEL TWA) [1]	999 mg/m <sup>3</sup>
WEL TWA (OEL TWA) [2]	400 ppm
WEL STEL (OEL STEL)	1250 mg/m <sup>3</sup>
WEL STEL (OEL STEL) [ppm]	500 ppm
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

#### 8.1.2. Recommended monitoring procedures

No additional information available

#### 8.1.3. Air contaminants formed

No additional information available

#### 8.1.4. DNEL and PNEC

No additional information available

#### 8.1.5. Control banding

No additional information available

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 8.2. Exposure controls

#### 8.2.1. Appropriate engineering controls

**Appropriate engineering controls:**

Ensure good ventilation of the work station.

#### 8.2.2. Personal protection equipment

**Personal protective equipment symbol(s):**



##### 8.2.2.1. Eye and face protection

**Eye protection:**

Safety glasses

##### 8.2.2.2. Skin protection

**Skin and body protection:**

Wear suitable protective clothing

**Hand protection:**

Protective gloves

##### 8.2.2.3. Respiratory protection

**Respiratory protection:**

In case of insufficient ventilation, wear suitable respiratory equipment

##### 8.2.2.4. Thermal hazards

No additional information available

#### 8.2.3. Environmental exposure controls

**Environmental exposure controls:**

Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Liquid.
Colour	: Blue.
Odour	: No data available
Odour threshold	: No data available
pH	: $\approx 8$
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: $\approx 0.95 \text{ g/cm}^3$
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Explosive properties : No data available  
Oxidising properties : No data available  
Explosive limits : No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified  
Acute toxicity (dermal) : Not classified  
Acute toxicity (inhalation) : Not classified

propan-2-ol; isopropyl alcohol; isopropanol (67-63-0)	
LD50 oral rat	4700 – 5800 mg/kg
LD50 dermal rabbit	13000 mg/kg
LC50 Inhalation - Rat [ppm]	10000 ppm/4h

Skin corrosion/irritation : Not classified  
pH: ≈ 8  
Serious eye damage/irritation : Not classified  
pH: ≈ 8  
Respiratory or skin sensitisation : Not classified  
Germ cell mutagenicity : Not classified  
Carcinogenicity : Not classified  
Reproductive toxicity : Not classified  
STOT-single exposure : Not classified

propan-2-ol; isopropyl alcohol; isopropanol (67-63-0)	
STOT-single exposure	May cause drowsiness or dizziness.

STOT-repeated exposure : Not classified  
Aspiration hazard : Not classified

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 12: Ecological information

#### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified

Not rapidly degradable

#### propan-2-ol; isopropyl alcohol; isopropanol (67-63-0)

LC50 - Fish [1]	9640 – 10400 mg/l
EC50 - Crustacea [1]	7550 – 13299 mg/l
IC50, algae	> 1000 (72 Hours)

#### 12.2. Persistence and degradability

No additional information available

#### 12.3. Bioaccumulative potential

#### propan-2-ol; isopropyl alcohol; isopropanol (67-63-0)

Bioaccumulative potential	Does not bioaccumulate.
---------------------------	-------------------------

#### 12.4. Mobility in soil

No additional information available

#### 12.5. Results of PBT and vPvB assessment

No additional information available

#### 12.6. Other adverse effects

No additional information available

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

### SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.2. UN proper shipping name</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.3. Transport hazard class(es)</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ADR	IMDG	IATA	ADN	RID
<b>14.4. Packing group</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.5. Environmental hazards</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

### 14.6. Special precautions for user

#### Overland transport

Not regulated

#### Transport by sea

Not regulated

#### Air transport

Not regulated

#### Inland waterway transport

Not regulated

#### Rail transport

Not regulated

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

#### 15.1.2. National regulations

##### France

#### Occupational diseases

Code	Description
RG 84	Conditions caused by liquid organic solvents for professional use: saturated or unsaturated aliphatic or cyclic liquid hydrocarbons and mixtures thereof; liquid halogenated hydrocarbons; nitrated derivatives of aliphatic hydrocarbons; alcohols; glycols, glycol ethers; ketones; aldehydes; aliphatic and cyclic ethers, including tetrahydrofuran; esters; dimethylformamide and dimethylacetamine; acetonitrile and propionitrile; pyridine; dimethylsulfone and dimethylsulfoxide

##### Germany

Employment restrictions

: Observe restrictions according Act on the Protection of Working Mothers (MuSchG)  
Observe restrictions according Act on the Protection of Young People in Employment (JArbSchG)

# GLASS & MIRROR CLEANER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Water hazard class (WGK) : WGK 1, Slightly hazardous to water (Classification according to AwSV, Annex 1)  
Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

### Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed  
SZW-lijst van mutagene stoffen : None of the components are listed  
NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Borstvoeding : None of the components are listed  
NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Vruchtbaarheid : None of the components are listed  
NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : None of the components are listed

### Denmark

Danish National Regulations : Pregnant/breastfeeding women working with the product must not be in direct contact with the product

## 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Full text of H- and EUH-statements	
Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Acute Tox. 4 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H225	Highly flammable liquid and vapour.
H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H336	May cause drowsiness or dizziness.
EUH210	Safety data sheet available on request.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.