


## MIRO 12.4 24V-2S OUTPUT RELAY




IN: 24 VAC/DC - OUT: 250 VAC/DC / 6 A

24 V AC/DC  
Screw terminals

### [Link to Product](#)

#### Illustration



*stay connected*

Product may differ from Image

### Approvals



### Utilization category

AC-12	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)

DC-13 1 A (24 V DC); 0.2 A (110 V DC); 0.1 A (230 V DC)

### Input

Connection voltage - current 24 VAC/DC (19.2...30 VAC/DC) - 20mA

LED display LED (green)

### General data

Mech./ elect. life 20.000.000 switching cycles/load dependent

Test isolation voltage 4 kV; safe separation (EN 60947-1)

Mounting method DIN-rail mountable (EN 60715)

Temperature range -20...+55 °C

Dimensions H x W x D 90x12.4x65 mm

### Output

Switching voltage max. 250 V AC/DC

Switching current per output max. 6 A

Min. load current 100 mA (12 V DC)

Power rating (voltage dependent) max. 1500 VA/120 W

Switching frequency max. 10 Hz

Contact material Ag Sn O<sub>2</sub>

Energize/release/contact bounce time 10/15/1.5 ms

### Commercial data

country of origin CZ

customs tariff number 85364900

minimum order quantity 1