

180° counterbore set, HSSE, uncoated for fine through hole
for universal use up to 1300 N/mm²



Application

For producing 180° counterbores of fine quality grade for through holes in accordance with DIN 74-2, type H, J, K and DIN 974-1.

Version

- profile-ground with spiral blade

Advantage

- spiral chip flutes ensure smooth cutting and the blade does not catch



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	30	20	10	10	10	70	80	45	40	40	40	30		15	7				

Art. No.	11445 500
Cutting material	HSSE
Version	For clearance hole M3/M4/M5/M6/M8/M10 fine quality grade
Composition of set	1 of each counterbore for M3/M4/M5/M6/M8/M10
DIN	373

EAN-Code

4050293068504