

Multi-range thread milling cutter with neck recess solid carbide straight shank HA

for universal use up to 1500 N/mm² in female threads

ATORN[®]

Application

For producing **metric** right-hand and left-hand threads on CNC machines in through holes and blind holes in the steel, stainless steel, non-ferrous metals, cast iron and special alloy material groups up to a strength of 1500 N/mm².



Version

- With collar recess.

Advantage

- Innovative cutting geometry for very high dimensional accuracy, process reliability and chip removal.
- Deep thread depth achievable due to collar recess between thread part and shank.

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	120	110	90		80	220	240			180	180	220	150	90	50	40	40		

Art. no.	13498 506
Tool holding device	HA parallel shank
Cutting material	VHM
Surface	TiAlN
Hole type	Clearance/blind hole ≤ 2xD
Coolant supply	Internal
Cutting edge diameter	10 mm
Pitch	1.5 mm
Suitable from thread size	MF13
Length	73 mm
Cutting edge length	18 mm
Effective length of thread milling	30 mm
Shaft diameter	10 mm
Number of cutting edges	4 PCS
f steel 1000	0.06 mm/r

EAN-Code

4050293264135