

Narrow disc milling cutter HSSE Co 5

Type N

ORION[®]

Application:

For slot milling and parting off

Version:

- Type A
- Fine cross-toothing
- Cuts on 3 sides
- Hole with longitudinal groove according to DIN 138



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	27	22	17	20	11	195	195	160	170	30	30	183		23	18	18	10		

Art. no.	14103 375
Type	N
Number of cutting edges	36 PCS
Milling cutter design standard	DIN 1834
Cutting edge diameter	100 mm
Bore diameter	32 mm
Width of cutting edge	1.6 mm
fz steel 700	0.06 mm

EAN-Code

4053625035014