

PCLN steel boring bar, negative, left
for facing and longitudinal turning using CN indexable insert

ATORN®

Application


for facing and longitudinal turning using CN 80° indexable insert

Version

- precision-manufactured steel boring bar, C type, 95° pitch angle, 80° tip angle, 0° clearance angle

Advantage

- universal use for facing and longitudinal turning
- negative body geometry ensures good stability and absorption of force for large cutting depths



Art. No.	17852 016
ISO name	S 25 T PCLN R/L 12
Min. bore diameter	31 mm
Shaft diameter	25 mm
Clearance length	40 mm
Length	300 mm
Clamping surface height	23 mm
Programming size	17 mm
Cutting edge height	11.5 mm
Suitable for indexable inserts	CN.. 1204..
Tool design	Left
DIN	8024

EAN-Code

4050293 126945