

Keysight Technologies U1730C Series Handheld LCR Meters

Take your expectations higher
with the latest LCR meters

[Data Sheet](#)





Introduction

The Keysight Technologies, Inc. U1730C Series handheld LCR meters allow you to measure at frequencies as high as 100 kHz—a capability typically found only in benchtop meters. Get measurements done faster using the one-touch automatic identification function button which displays component type and more detailed component analysis such as Z, ESR, and DCR. Ideal for testing on the go, these LCR meters operate on a battery that lasts up to 16 hours. With the U1730C Series that is built for your convenience, you can perform quick and basic LCR measurements at an affordable price.

Features

Key features

- 20,000 counts resolution
- 0.2% basic accuracy
- Wide LCR ranges with three to five selectable test frequencies (up to 100 kHz for U1733C)
- Auto identification (Ai) automatically determines and displays component type and measurements
- Detailed component analysis with DCR, ESR, Z, D, Q, and θ functions
- Battery life of 16 hours/AC-powered
- IR-to-USB connectivity for data logging to PC

Frequency up to 100 kHz

The test frequency now extends as high as 100 kHz, providing more flexibility to test a wider range of components. A higher test frequency, for example 100 kHz, is useful for applications such as testing aluminum electrolytic capacitors used in switching power supply circuits.

Automated identification

With Ai the testing and measuring experience is easy; eliminating unnecessary trial and error time—with just a single push of a button. This unique feature automatically specifies L, C, or R with parallel and series mode, without the need to manually change buttons.

Detailed component analysis

The handheld LCR meters allows you to test various component types, including secondary components of Dissipation Factor (D), Quality Factor (Q), and Angle Indication of Impedance (θ). This new handheld series also includes other functions that result in a more detailed component analysis. For example, the built-in Equivalent Series Resistance (ESR) function helps you better understand the inherent resistance behavior typically found in capacitors across selected frequencies. DCR is a built-in DC resistance measurement that eliminates the use of a separate digital multimeter (DMM) for component test.



Figure 1. Automate the recording of continuous readings when you hook the U1731C/U1732C/U1733C to a PC

Take a Closer Look



Figure 2. Front view of the U1733C

U1731C/U1732C/U1733C Electrical Specifications

Accuracy is given as \pm (% of reading + counts of least significant digit) at 23 °C \pm 5 °C, with relative humidity less than 80%. Please refer to the User Guide about the measuring mode specified for each range of L/C/R, series or parallel mode. Measurements performed at the test socket and necessary Open and Short corrections must prior be done. The accuracy is verified by design and specified type tests.

Impedance/Resistance		Accuracy = AZ + Offset					
Range	Resolution	U1731C/U1732C/U1733C			U1732C/U1733C		U1733C
		100 Hz	120 Hz	1 kHz	10 kHz	100 kHz	DCR
2 Ω ¹	0.0001 Ω	0.7% + 50	0.7% + 50	0.7% + 50	0.7% + 50	1.0% + 50	0.7% + 50
20 Ω ¹	0.001 Ω	0.7% + 8	0.7% + 8	0.7% + 8	0.7% + 8	0.7% + 8	0.7% + 8
200 Ω ¹	0.01 Ω	0.2% + 3	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 5	0.2% + 3
2000 Ω	0.1 Ω	0.2% + 3	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 5	0.2% + 3
20 k Ω	0.001 k Ω	0.2% + 3	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 5	0.2% + 3
200 k Ω	0.01 k Ω	0.5% + 5	0.5% + 5	0.5% + 5	0.5% + 5	0.7% + 8	0.5% + 5
2000 k Ω	0.1 k Ω	0.5% + 5	0.5% + 5	0.5% + 5	0.7% + 5	NA	0.5% + 5
20 M Ω	0.001 M Ω	2.0% + 8	2.0% + 8	2.0% + 8	5.0% + 8	NA	2.0% + 8
200 M Ω	0.01 M Ω	6.0% + 80	6.0% + 80	6.0% + 80	NA	NA	6.0% + 80

The accuracy for ranges 2 Ω to 200 Ω is specified after Null function is used to subtract the resistance of test leads and the contact resistance.

Notes:

- For the ranges of 20 M Ω and 200 M Ω , the R.H. is specified for < 60%
- Resistance is specified to $Q < 10$ and $D > 0.1$, otherwise the accuracy is $(AZ + Offset) \times \sqrt{1 + Q^2}$
- Equivalence Series Resistance (ESR) measurement is determined by impedance measurement and range. The maximum display is up to 199.99 k Ω and the accuracy is $(AZ + Offset) \times \sqrt{1 + Q^2}$

Capacitance		Accuracy = AC + Offset				
Range	Resolution	U1731C/U1732C/U1733C			U1732C/U1733C	U1733C
		100 Hz	120 Hz	1 kHz	10 kHz	100 kHz
20 mF	0.001 mF	0.5% + 8	0.5% + 8	NA	NA	NA
2000 μ F	0.1 μ F	0.5% + 5	0.5% + 5	0.5% + 8	NA	NA
200 μ F	0.01 μ F	0.3% + 3	0.3% + 3	0.5% + 5	0.5% + 8	NA
20 μ F	0.001 μ F	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 5	5.0% + 10
2000 nF	0.1 nF	0.2% + 3	0.2% + 3	0.2% + 3	0.2% + 3	0.7% + 10
200 nF	0.01 nF	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 3	0.7% + 10
20 nF	0.001 nF	0.5% + 5	0.5% + 5	0.2% + 3	0.5% + 3	0.7% + 10
2000 pF1	0.1 pF	0.5% + 10	0.5% + 10	0.5% + 5	0.5% + 3	2.0% + 10
200 pF1	0.01 pF	NA	NA	0.5% + 10	0.8% + 10	2.0% + 10
20 pF1	0.001 pF	NA	NA	NA	1.0% + 20	2.5% + 10

This accuracy for the ranges of 20 pF~2000 pF is specified after Math Null which is used to substrate the stray capacitances for test leads.

Notes:

- The accuracy for the ceramic capacitor will be influenced depending on the dielectric constant (K) of the material used to make the ceramic capacitor. For related influence factors, please refer to the Component dependency factors section in the Impedance Measurement Handbook, downloadable for free at <http://www.keysight.com/find/lcrmeters>

U1731C/U1732C/U1733C Electrical Specifications

Inductance						
Range	Resolution	Accuracy = AL + Offset				
		U1731C/U1732C/U1733C			U1732C/U1733C	U1733C
		100 Hz	120 Hz	1 kHz	10 kHz	100 kHz
20 μ H	0.001 μ H	NA	NA	NA	1.0% + 5	2.5% + 20
200 μ H	0.01 μ H	NA	NA	1.0% + 5	0.7% + 3	2.5% + 20
2000 μ H	0.1 μ H	0.7% + 10	0.7% + 10	0.5% + 3	0.5% + 3	0.8% + 20
20 mH	0.001 mH	0.5% + 3	0.5% + 3	0.2% + 3	0.3% + 3	0.8% + 10
200 mH	0.01 mH	0.5% + 3	0.5% + 3	0.2% + 3	0.2% + 3	1.0% + 10
2000 mH	0.1 mH	0.2% + 3	0.2% + 3	0.2% + 3	0.5% + 5	1.0% + 10
20 H	0.001 H	0.2% + 3	0.2% + 3	0.5% + 5	1.0% + 5	2.0% + 10
200 H	0.01 H	0.7% + 5	0.7% + 5	1.0% + 5	2.0% + 8	NA
2000 H	0.1 H	1.0% + 5	1.0% + 5	2.0% + 8	NA	NA

Phase Angle of Impedance				
Range	Resolution	Accuracy (θ_e)	Condition	
-180° ~180°	0.1°/1°	(AZ + Offset/Zx) x 180/ π	D < 1 or Q > 1	
Impedance	Zx	AZ	Offset	θ_e
1999.9 Ω	19999	0.2%	3	$\pm 0.12^\circ$
199.9 Ω	1999	0.2%	3	$\pm 0.20^\circ$
19.9 Ω	199	0.2%	3	$\pm 0.98^\circ$
1.9 Ω	19	0.2%	3	$\pm 9.16^\circ$

Notes:

- Specifications are applicable to all models (U1731C, U1732C, and U1733C) unless specified
- The “AZ” and Offset are the accuracy specified at impedance
- The “ π ” is approximately 3.14159

Dissipation/Quality Factor				
Function	Range	Accuracy (De)	Condition	
Z	0.001~999	AZ + Offset/Zx x 100% + 3	D < 1 or Q > 1	
L	0.001~999	AL + Offset/Lx x 100% + 3	D < 1 or Q > 1	
C	0.001~999	AC + Offset/Cx x 100% + 3	D < 1 or Q > 1	
Capacitance	Cx	AC	Offset	De
88.88 μ F	8888	0.2%	3	0.334% + 3

Notes:

- Specifications are applicable to all models (U1731C, U1732C, and U1733C) unless specified
- The “AZ, AL, AC” and Offset are the accuracy specified at Impedance, Inductance, and Capacitance, respectively
- The Zx, Lx, and Cx are the display count of the reading. For example, the Cx is 8888 as if the capacitance is 88.88 μ F for the range of 200 μ F.
- The Quality Factor is the reciprocal of Dissipation Factor

U1731C/U1732C/U1733C Electrical Specifications

Test Signal		Test signal level		Test frequency	
Model	Selection	Level	Accuracy	Frequency	Accuracy
U1731C/U1732C/U1733C	100 Hz	0.74 Vrms	0.05 Vrms	100 Hz	0.01%
	120 Hz	0.74 Vrms	0.05 Vrms	120.481 Hz	0.01%
	1 kHz	0.74 Vrms	0.05 Vrms	1 kHz	0.01%
U1732C/1733C	10 kHz	0.70 Vrms	0.05 Vrms	10 kHz	0.01%
U1733C	100 kHz	0.70 Vrms	0.05 Vrms	100 kHz	0.01%
	DCR	+1.235 V	0.05 V	NA	NA

Source Impedance of Impedance/Resistance Measurement						
Range	Typical source impedance					
	U1731C/U1732C/U1733C			U1732C/U1733C		U1733C
	100 Hz	120 Hz	1 kHz	10 kHz	100 kHz	DCR
2 Ω	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω
20 Ω	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω
200 Ω	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω
2000 Ω	1 kΩ	1 kΩ	1 kΩ	1 kΩ	1 kΩ	1 kΩ
20 kΩ	10 kΩ	10 kΩ	10 kΩ	10 kΩ	1 kΩ	10 kΩ
200 kΩ	100 kΩ	100 kΩ	100 kΩ	10 kΩ	1 kΩ	100 kΩ
2000 kΩ	100 kΩ	100 kΩ	100 kΩ	10 kΩ	NA	100 kΩ
20 MΩ	100 kΩ	100 kΩ	100 kΩ	100 kΩ	NA	100 kΩ
200 MΩ	100 kΩ	100 kΩ	100 kΩ	NA	NA	100 kΩ

Source Impedance of Capacitance Measurement					
Range	Typical source impedance				
	U1731C/U1732C/U1733C			U1732C/U1733C	U1733C
	100 Hz	120 Hz	1 kHz	10 kHz	100 kHz
20 mF	100 Ω	100 Ω	NA	NA	NA
2000 μF	100 Ω	100 Ω	100 Ω	NA	NA
200 μF	100 Ω	100 Ω	100 Ω	100 Ω	NA
20 μF	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω
2000 nF	1 kΩ	1 kΩ	100 Ω	100 Ω	100 Ω
200 nF	10 kΩ	10 kΩ	1 kΩ	100 Ω	100 Ω
20 nF	100 kΩ	100 kΩ	10 kΩ	1 kΩ	100 Ω
2000 pF	100 kΩ	100 kΩ	100 kΩ	10 kΩ	1 kΩ
200 pF	NA	NA	100 kΩ	10 kΩ	1 kΩ
20 pF	NA	NA	NA	100 kΩ	1 kΩ

U1731C/U1732C/U1733C Electrical Specifications

Source Impedance of Inductance Measurement					
Range	Typical source impedance				
	U1731C/U1732C/U1733C			U1732C/U1733C	U1733C
	100 Hz	120 Hz	1 kHz	10 kHz	100 kHz
20 μ H	NA	NA	NA	100 Ω	100 Ω
200 μ H	NA	NA	100 Ω	100 Ω	100 Ω
2000 μ H	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω
20 mH	100 Ω	100 Ω	100 Ω	100 Ω	100 Ω
200 mH	100 Ω	100 Ω	100 Ω	1 k Ω	1 k Ω
2000 mH	100 Ω	100 Ω	1 k Ω	10 k Ω	1 k Ω
20 H	1 k Ω	1 k Ω	10 k Ω	10 k Ω	1 k Ω
200 H	10 k Ω	10 k Ω	100 k Ω	100 k Ω	NA
2000 H	100 k Ω	100 k Ω	100 k Ω	NA	NA

General Specifications

Parameter	U1731C	U1732C	U1733C
Measurements	Z/L/C/R/D/Q/θ/ESR	Z/L/C/R/D/Q/θ/ESR	Z/L/C/R/D/Q/θ/ESR/DCR
Display	Primary display: Maximum display 19,999 counts Secondary display: Maximum display 999 counts Automatic polarity indication		
Test frequency (Accuracy = ± 0.1% of actual test frequency)	100 Hz, 120 Hz, 1 kHz	100 Hz, 120 Hz, 1 kHz, 10 kHz	100 Hz, 120 Hz, 1 kHz, 10 kHz, 100 kHz
Backlight	No	Yes	Yes
Test signal level	Selection	Test signal level	Test frequency
	100 Hz	0.74 Vrms	100 Hz
	120 Hz	0.74 Vrms	120.481 Hz
	1 kHz	0.74 Vrms	1 kHz
	10 kHz ¹	0.74 Vrms	10 kHz
	100 kHz ²	0.74 Vrms	100 kHz
	DCR ²	+1.235 V	NA
Tolerance mode	1%, 5%, 10%, 20%		
Ranging mode	Auto and manual		
Measurement rate	1 time/second, nominal		
Response time	Approximately 1 second/DUT (Device Under Test)		
Auto power-off	~0-99 mins without operation		
Power supply	Single standard 9 V battery (alkaline or carbon-zinc) or optional power adaptor		
Power consumption	225 mVA maximum without backlight		
Input protection fuse	Resettable over-current protection		
Battery life	16 hours based on alkaline battery		
Low battery indicator	[] will appear when voltage drops below ~7.2 V		
Operating temperature	-10 to 55 °C, 0 to 80% R.H.		
Storage temperature	-20 to 70 °C, 0 to 80% R.H. without battery		
Temperature coefficient	0.1 × (specified accuracy)/°C (from -10 to 18 °C or 28 to 55 °C)		
Relative humidity	Maximum 80% R.H. for temperature up to 30 °C decreasing linearly to 50% R.H. at 55 °C		
Weight	337 grams with battery		
Dimensions (H x W x D)	184 mm x 87 mm x 41 mm		
Safety and EMC Compliance	In compliance with EN61010-1 (IEC61010-1:2001) for low voltage directive and Pollution Degree II Environment. Susceptibility and Emissions (EMC): Commercial Limits per EN61326-1		
Calibration	One-year calibration cycle recommended		
Warranty	3 years for main unit 3 months for standard shipped accessories		

Only applicable for U1732C/U1733C

Only applicable for U1733C

Ordering Information



Standard Shipped Items

- Standard U1731C, U1732C, and U1733C ordering include:
- Quick Start Guide
 - Certificate of Calibration (CoC)
 - Alligator clip leads
 - 9 V alkaline battery

Recommended Accessories

U1731P



- Combo Kit
Includes one U1731C Series handheld and four accessories:
- U5491A soft carrying case
 - U5481B IR-to-USB cable
 - U1780A AC adaptor
 - U1782B SMD tweezers

U1732P



- Combo Kit
Includes one U1732C Series handheld and four accessories:
- U5491A soft carrying case
 - U5481B IR-to-USB cable
 - U1780A AC adaptor
 - U1782B SMD tweezers

U1733P



- Combo Kit
Includes one U1733C Series handheld and four accessories:
- U5491A soft carrying case
 - U5481B IR-to-USB cable
 - U1780A AC adaptor
 - U1782B SMD tweezers

U1174A



Soft carrying case

U5481B



IR-to-USB cable

U1782B



SMB tweezers

U1780A



Power adaptor and cord (according to country)

U1781A



Alligator clip leads

Evolving

Our unique combination of hardware, software, support, and people can help you reach your next breakthrough. **We are unlocking the future of technology.**



From Hewlett-Packard to Agilent to Keysight



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:
www.keysight.com/find/contactus
 (BP-10-3-16)



www.keysight.com/go/quality
 Keysight Technologies, Inc.
 DEKRA Certified ISO 9001:2015
 Quality Management System

myKeysight

myKeysight
www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
 Lower costs.

Keysight Services
www.keysight.com/find/service

Our deep offering in design, test, and measurement services deploys an industry-leading array of people, processes, and tools. The result? We help you implement new technologies and engineer improved processes that lower costs.



Three-Year Warranty
www.keysight.com/find/ThreeYearWarranty

Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



Keysight Assurance Plans
www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners
www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/handheldlcr



Unlocking Measurement Insights

This information is subject to change without notice.
 © Keysight Technologies, 2013 - 2017
 Published in USA, January 5, 2017
 5990-7778EN
www.keysight.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keysight:](#)

[U1731C](#) [U5481B](#) [U1732C](#) [U1733C](#)