


PHYSICAL DIMENSIONS:

A	3.20 [.126]	+ 0.20 [.008]
B	1.60 [.063]	+ 0.20 [.008]
C	0.80 [.031]	+ 0.20 [.008]
D	0.40 [.016]	+ 0.15 [.006]
D1	0.30 [.012]	+ 0.20 [.008]
E	0.80 [.031]	+ 0.10 [.004]



DA1206D301R-10

UNCONTROLLED DOCUMENT




ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	300	
Minimum	225	
Maximum	375	0.4
LINE TO LINE INSULATION RESISTANCE >100 MΩ AT 75 VOLTS.		




LAND PATTERNS FOR REFLOW SOLDERING



(For wave soldering, add 0.762 (0.030) to this dimension)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
C	UPDATE COMPANY LOGO	05/21/09	JRK	DA1206D301R-10	REV C	PART TYPE: CO-FIRE	DRAWN BY: TMB
B	D1 chgd from 0.008 ±0.004 to 0.012 ±0.008. ADD ROHS, UPDATE COMPANY LOGO	10/31/07	JRK	DATE: 03/30/04	SCALE: NTS	SHEET: 2 of 2	
A	ORIGINAL DRAFT	03/30/04	TMB	CAD # DA1206D301R-10-C	TOOL # -		
REV	DESCRIPTION	DATE	INT				