

## Fixed centring point

With full tip and thread for draw-off nuts



### Application:

For centring workpieces on lathes, grinding machines and radial drilling machines.

### Execution:

- Tip angle 60°.
- With thread for draw-off nut.
- Taper fully hardened and precision-ground.
- Carbide-tipped.
- Concentricity tolerance  $\leq 0.8 \mu\text{m}$ .

### Delivery:

1x centring point MK 2.



<b>Art. no.</b>	<b>22121 140</b>
<b>Brand</b>	BRUCKNER
<b>Manufacturer Part Number</b>	2854
<b>Morse taper size</b>	MK 4
<b>Programming size</b>	72.5 mm
<b>Diameter of flat area</b>	14 mm
<b>Nut for removing spindles</b>	M36 x 1.5
<b>Concentricity tolerance</b>	0.008 mm
<b>DIN</b>	807
<b>Gross Weight</b>	0.899 kg
<b>Product Group</b>	2AA