Miniature Enclosed Limit Switches



RoHS Compliant

Characteristics

	Degree of protection	IP65		
Rating	IEC 60947-5-1	AC-12 250V AC / 5A, DC-12 125V DC / 0.4A		
_	UL508	250V AC / 15A, 125V DC / 0.4A		
	Mechanical	10,000,000 operations min.		
Durability	Electrical	300,000 operations min. (5A at 250V AC, resistive load)		
	Operating Speed	5mm ~ 0.5m/s		
0 " "	Mechanical	120 operations /min.		
Operating Frequency	Electrical	30 operations /min.		
	Rated Frequency	50/60Hz		
	Insulation Resistance	100MΩ min. (at 500V DC)		
	Contact Resistance	25mΩ max. (Initial value)		
Dielectric Strength	Between terminals of same polarity	1,000V AC 50/60Hz for 1min		
	Between current-carrying metal parts and ground	1,500V AC 50/60Hz for 1min		
	Rated insulation voltage (Ui)	250V		
Pol	Pollution degree (Application environment) 3 (EN60947-5-1)			
Conditional short-circuit current 1		100A(EN60947-5-1)		
	Rated open thermal current (Ith)	5A(EN60947-5-1)		
	Electric shock protection class Class I			
Vibration Resistance	Malfunction	10~55 Hz 1.5mm double amplitude		
Shock Resistance	Destruction	1,000m/s ² (free position) min.		
SHOCK RESISTANCE	Malfunction	300m/s ² (operation limit position) min		
Ambient operating temperature range -20°C ~ +60°C with r				
	Ambient operating humidity range	90% RH Max.		

Notes:

- 1. Above values of these characteristics are initial values.
- 2. Above values of these characteristics may are depending on different models.
- 3. Above durability is for an ambient temperature of 5 to 35° and ambient humidity of 40% to 70%.

Operating Characteristics

Part Number	Operating Force (Max.)	Release Force (Min.)	Pre Travel (Max.)	Over Travel (Min.)	Movement Differential (Max.)	TTP	Operating Position
MC002421	9.8N	2.94N	1.5mm	4mm	1.2mm	5.5mm	26 ±0.8mm
MC002422	9.8N	2.94N	1.5mm	4mm	1.2mm	5.5mm	37 ±0.8mm

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro






Part Number	Operating Force (Max.)	Release Force (Min.)	Pre Travel (Max.)	Over Travel (Min.)	Movement Differential (Max.)	TTP	Operating Position
MC002423	9.8N	2.94N	1.5mm	4mm	1.2mm	5.5mm	37 ±0.8mm
MC002424	5.88N	0.49N	20°	75°	10°	95°	-
MC002425	7.84N	0.49N	20°	75°	10°	95°	-
MC002426	5.88N	0.69N	20°	75°	10°	95°	-
MC002427	0.88N	-	30mm	-	-	-	-
MC002428	0.88N	-	30mm	-	-	-	-

Sealed Push Plunger



MC002421


Weight: 116.4g



Sealed Roller Plunger




MC002422 Weight: 121.7g



Sealed Crossroller Plunger




MC002423 Weight: 122g



Standard Roller Lever



MC002424 Weight: 147.4g



Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Miniature Enclosed Limit Switches Multicomp PRO

Adjustable Roller Lever




MC002425

Weight: 120.5g

Adjustable Rod Lever




Weight: 158.8g



Omnidirectional Coil Spring




Weight: 114g



Omnidirectional Wire Spring



Weight: 112.5g



Dimensions: Millimetres

Part Number Table

Description			
Vertical Limit Switch, Miniature Enclosed (IP65), Sealed Push Plunger, Screw Terminal	MC002421		
Vertical Limit Switch, Miniature Enclosed (IP65), Sealed Roller Plunger, Screw Terminal	MC002422		
Vertical Limit Switch, Miniature Enclosed (IP65), Sealed Crossroller Plunger, Screw Terminal	MC002423		
Vertical Limit Switch, Miniature Enclosed (IP65), Standard Roller Lever, Screw Terminal	MC002424		
Vertical Limit Switch, Miniature Enclosed (IP65), Adjustable Roller Plunger, Screw Terminal	MC002425		
Vertical Limit Switch, Miniature Enclosed (IP65), Adjustable Rod Lever, Screw Terminal	MC002426		
Vertical Limit Switch, Miniature Enclosed (IP65), Omnidirectional Coil Spring, Screw Terminal	MC002427		
Vertical Limit Switch, Miniature Enclosed (IP65), Omnidirectional Wire Spring, Screw Terminal	MC002428		

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



08/05/20 V1.0