

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 27.01.2020

version number 3

Revision: 27.01.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking***1.1 Product identifier**

***Trade name:** S200 KINEMATIC VISCOSITY, DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

***Article number:** REVISC-S200

***CAS Number:**
68037-01-4

***Registration number**

A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

***1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

***Application of the substance / the mixture** Laboratory Chemicals

1.3 Details of the supplier of the safety data sheet**Manufacturer/Supplier:**

Reagecon Diagnostics Ltd.
Shannon Free Zone,
Shannon,
Co. Clare,
Ireland.
Tel +353 61 472622
Fax +353 61 472642

***Further information obtainable by contacting:** sds@reagecon.ie

***1.4 Emergency telephone number:**

For Hazardous Materials [or Dangerous Goods] Incident
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC
For Ireland call +(353)-19014670
For Outside Ireland call +1 703-741-5970 / 1-800-424-9300 CCN849800

SECTION 2: Hazards identification***2.1 Classification of the substance or mixture**

***Classification according to Regulation (EC) No 1272/2008**

Aquatic Chronic 4 H413 May cause long lasting harmful effects to aquatic life.

***2.2 Label elements**

***Labelling according to Regulation (EC) No 1272/2008**

The substance is classified and labelled according to the CLP regulation.

***Hazard pictograms** Void

***Signal word** Void

***Hazard statements**

H413 May cause long lasting harmful effects to aquatic life.

***Precautionary statements**

P273 Avoid release to the environment.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

***2.3 Other hazards**

***Results of PBT and vPvB assessment**

***PBT:** Not applicable.

***vPvB:** Not applicable.

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 27.01.2020

version number 3

Revision: 27.01.2020

Trade name: S200 KINEMATIC VISCOSITY, DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

(Contd. of page 1)

SECTION 3: Composition/information on ingredients

***3.1 Chemical characterisation: Substances**

***CAS No. Description**

68037-01-4 1-Decene, homopolymer, hydrogenated

SECTION 4: First aid measures

***4.1 Description of first aid measures**

***After inhalation:**

Provide fresh air, warmth and rest. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Obtain medical attention if any discomfort continues.

***After skin contact:** Generally the product does not irritate the skin.

***After eye contact:**

Promptly wash eyes with plenty of water for up to 15 minutes. Open eyes wide apart and rinse well to remove any contact lenses. Do not remove contact lenses by hand. Continue to rinse. Get medical attention if symptoms persist.

***After swallowing:** If symptoms persist consult doctor.

***4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.

***4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

***5.1 Extinguishing media**

***Suitable extinguishing agents:**

Indications shall be given whether any extinguishing media are inappropriate for a particular situation involving the substance or mixture

Use fire extinguishing methods suitable to surrounding conditions.

***5.2 Special hazards arising from the substance or mixture** No further relevant information available.

***5.3 Advice for firefighters**

***Protective equipment:**

Fire fighters should wear complete protective clothing including self-contained breathing apparatus. Do not breathe fumes. Keep containers cool by spraying with water if exposed to fire. Avoid run off to waterways and sewers

SECTION 6: Accidental release measures

***6.1 Personal precautions, protective equipment and emergency procedures**

Wear protective equipment as described in Section 8 below. Keep unprotected persons away.

***6.2 Environmental precautions:**

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

***6.3 Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

***6.4 Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

IE

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 27.01.2020

version number 3

Revision: 27.01.2020

Trade name: S200 KINEMATIC VISCOSITY, DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

(Contd. of page 2)

SECTION 7: Handling and storage

***7.1 Precautions for safe handling**

Keep receptacles tightly sealed.

No special precautions are necessary if used correctly.

***Information about fire - and explosion protection:** No special measures required.

***7.2 Conditions for safe storage, including any incompatibilities**

***Storage:**

***Requirements to be met by storerooms and receptacles:** No special requirements.

***Information about storage in one common storage facility:** Not required.

***Further information about storage conditions:** None.

***7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

***8.1 Control parameters**

***Ingredients with limit values that require monitoring at the workplace:** Not required.

***Additional information:** The lists valid during the making were used as basis.

***8.2 Exposure controls**

***Personal protective equipment:**

***General protective and hygienic measures:** Wash hands before breaks and at the end of work.

***Respiratory protection:**

Where risk assessment shows air-purifying respirators are appropriate use a respirator with multi-purpose combination (US) or type ABEK (EN14387) respirator cartridges as back up to engineering controls. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

***Protection of hands:**

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Always ensure that gloves are inspected before use.

Selection of protective gloves must include consideration of the penetration times along with rates of diffusion and degradation. The selected glove should comply with the specifications of EU Directive 89/686/EEC and the standard EN374 derived from it.

***Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

***Penetration time of glove material**

In the absence of data above, the exact break through time has to be sourced from the manufacturer of the protective gloves and has to be observed.

***Eye protection:**



Goggles recommended during refilling: Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU)

***Engineering Controls:** No further data; see item 7.

IE

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 27.01.2020

version number 3

Revision: 27.01.2020

Trade name: S200 KINEMATIC VISCOSITY, DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

(Contd. of page 3)

SECTION 9: Physical and chemical properties

*9.1 Information on basic physical and chemical properties

*General Information

*Appearance:

Form:	Liquid
Colour:	Colourless
*Odour:	Characteristic
*Odour threshold:	Not determined.

***pH-value:** Not determined.

*Change in condition

Melting point/freezing point:	Undetermined.
Initial boiling point and boiling range:	133 °C

***Flash point:** 264 °C

***Flammability (solid, gas):** Not applicable.

***Decomposition temperature:** Not determined.

***Auto-ignition temperature:** Not determined.

***Explosive properties:** Product does not present an explosion hazard.

*Explosion limits:

Lower:	Not determined.
Upper:	Not determined.

***Vapour pressure at 20 °C:** <0.000001 hPa

***Density at 20 °C:** 0.83 g/cm³

***Relative density** Not determined.

***Vapour density** Not determined.

***Evaporation rate** Not determined.

***Solubility/ miscibility with water:**

Not miscible or difficult to mix.

***Partition coefficient: n-octanol/water:** Not determined.

*Viscosity:

Dynamic:	Not determined.
Kinematic:	Not determined.

***9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

***10.1 Reactivity** No further relevant information available.

***10.2 Chemical stability**

***Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.

***10.3 Possibility of hazardous reactions** No dangerous reactions known.

***10.4 Conditions to avoid** No further relevant information available.

***10.5 Incompatible materials:** No further relevant information available.

***10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

*11.1 Information on toxicological effects

***Acute toxicity** Based on available data, the classification criteria are not met.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 27.01.2020

version number 3

Revision: 27.01.2020

Trade name: S200 KINEMATIC VISCOSITY, DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

(Contd. of page 4)

- ***Primary irritant effect:**
- ***Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- ***Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- ***Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- ***CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- ***Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- ***Carcinogenicity** Based on available data, the classification criteria are not met.
- ***Reproductive toxicity** Based on available data, the classification criteria are not met.
- ***STOT-single exposure** Based on available data, the classification criteria are not met.
- ***STOT-repeated exposure** Based on available data, the classification criteria are not met.
- ***Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- ***12.1 Toxicity**
- ***Aquatic toxicity:** No further relevant information available.
- ***12.2 Persistence and degradability** No further relevant information available.
- ***12.3 Bioaccumulative potential** No further relevant information available.
- ***12.4 Mobility in soil** No further relevant information available.
- ***Additional ecological information:**
- ***General notes:**
Water hazard class 1 (German Regulation) (Assessment by list): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- ***12.5 Results of PBT and vPvB assessment**
- ***PBT:** Not applicable.
- ***vPvB:** Not applicable.
- ***12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- ***13.1 Waste treatment methods**
 - ***Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- | | |
|----------------------------------|----------|
| *European waste catalogue | |
| HP14 | Ecotoxic |
- ***Uncleaned packaging:**
 - ***Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- | | |
|--|------|
| * 14.1 UN-Number | |
| * ADR, IMDG, IATA | Void |
| * 14.2 UN proper shipping name | |
| * ADR, IMDG, IATA | Void |
| * 14.3 Transport hazard class(es) | |
| * ADR, IMDG, IATA | |
| * Class | Void |

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing 27.01.2020

version number 3

Revision: 27.01.2020

Trade name: S200 KINEMATIC VISCOSITY, DYNAMIC VISCOSITY AND DENSITY STANDARD TO 100°C

(Contd. of page 5)

*14.4 Packing group *ADR, IMDG, IATA	Void
*14.5 Environmental hazards: *Marine pollutant:	No
*14.6 Special precautions for user	Not applicable.
*14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
*Transport/Additional information:	Not dangerous according to the above specifications.
*UN "Model Regulation":	Void

SECTION 15: Regulatory information

- *15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- *Directive 2012/18/EU
- *Named dangerous substances - ANNEX I Substance is not listed.
- *REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- *National regulations:
- *Waterhazard class: Water hazard class 1 (Assessment by list): slightly hazardous for water.
- *15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- *Department issuing SDS: Health and Safety
- *Contact: sds@reagecon.ie
- *Abbreviations and acronyms:
REACH (Registration, Evaluation, Authorisation and restriction of Chemicals)
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
CAS: Chemical Abstracts Service (division of the American Chemical Society)
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Aquatic Chronic 4: Hazardous to the aquatic environment - long-term aquatic hazard – Category 4
- *NO