

# KERN PCB 2000-1-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0



Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,3 g
Maximum creep (15 minutes)	400 mg
Maximum creep (30 minutes)	800 mg

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display screen size	89×30 mm
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English Symbol language

## Construction

Dimension housing (W×D×H)	163×245×65 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	130×130 mm
Transport safety lock - bolt torque	0,4 Nm
Levelling feet adjustable	✓

## Functions

Number of keys for operation	5
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)

## Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PCB

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	2000 g
Readability [d]	0,1 g
Resolution	20.000
Linearity	± 0,2 g
Reproducibility	0,1 g
Default unit	g

Units	kg
	g
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz
	ffa
m	

Adjustment options	Adjusting with external weight
Recommended adjusting weight	2 kg (M1)
Possible calibration points	500 g; 1 kg; 2 kg
Stabilization time	3 s

# KERN PCB 2000-1-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0

Underfloor weighing	Hook (included in delivery)
Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)
IP protection - display	no IP protection

## Counting

Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, free, Input
Counting resolution (laboratory conditions)	10.000

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Battery	4×1.5 V AA
Battery / accumulator type	Li-Ion
Battery connection	Battery insert
Battery operating time	20 h

## Environmental conditions

Humidity of environment [Max]	80 %
-------------------------------	------

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	235×365×175 mm
Net weight	1,4 kg
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	2,0 kg
Shipping weight	3 kg

## Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

