

CLEENOL

For a cleaner, safer world

SAFETY DATA SHEET GREEN PINE DISINFECTANT

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	GREEN PINE DISINFECTANT
Internal identification	062902X5
Container size	2x5L

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Disinfectant.
-----------------	---------------

1.3. Details of the supplier of the safety data sheet

Supplier	Cleenol Group Ltd Neville House Beaumont Road Banbury Oxon OX16 1RB UK Tel: +44 (0)1295 251721 sales@cleenol.co.uk
----------	---

1.4. Emergency telephone number

Emergency telephone	In case of a medical emergency following exposure to a chemical, call NHS Direct in England or Wales 0845 46 47 or NHS 24 in Scotland 08454 24 24 24 (UK only).
---------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards	Not Classified
Health hazards	Not Classified
Environmental hazards	Aquatic Chronic 3 - H412

2.2. Label elements

Hazard statements	EUH208 Contains DIPENTENE. May produce an allergic reaction. H412 Harmful to aquatic life with long lasting effects.
Precautionary statements	P273 Avoid release to the environment. P501 Dispose of contents/ container in accordance with national regulations.

2.3. Other hazards

GREEN PINE DISINFECTANT

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Alkyl (C12-16) dimethylbenzyl ammonium chloride (ADBAC/BKC (C12-16))	0.75%
CAS number: 68424-85-1	EC number: 270-325-2
M factor (Acute) = 10	M factor (Chronic) = 1

Classification

Acute Tox. 4 - H302
 Skin Corr. 1A - H314
 Eye Dam. 1 - H318
 Aquatic Acute 1 - H400
 Aquatic Chronic 1 - H410

DIPENTENE

<1%

CAS number: 138-86-3	EC number: 205-341-0
M factor (Acute) = 1	M factor (Chronic) = 1

Classification

Flam. Liq. 3 - H226
 Skin Irrit. 2 - H315
 Skin Sens. 1 - H317
 Aquatic Acute 1 - H400
 Aquatic Chronic 1 - H410

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Unlikely route of exposure as the product does not contain volatile substances.
Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Get medical attention if a large quantity has been ingested.
Skin contact	Rinse with water.
Eye contact	Remove any contact lenses and open eyelids wide apart. Rinse with water.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	No adverse effects known.
Ingestion	No harmful effects expected from quantities likely to be ingested by accident. No adverse effects known.
Skin contact	The product is considered to be a low hazard under normal conditions of use. May cause skin sensitisation or allergic reactions in sensitive individuals.
Eye contact	No adverse effects known. May be slightly irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations.
Specific treatments	Treat symptomatically.

GREEN PINE DISINFECTANT

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media None known.

5.2. Special hazards arising from the substance or mixture

Specific hazards Irritating gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting Fight fire with normal precautions from a reasonable distance.

Special protective equipment for firefighters Use protective equipment appropriate for surrounding materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Do not touch or walk into spilled material. Take care as floors and other surfaces may become slippery.

6.2. Environmental precautions

Environmental precautions Avoid discharge to the aquatic environment. Avoid contamination of ponds or watercourses with washing down water.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Absorb in vermiculite, dry sand or earth and place into containers. Discharge of small quantities to the sewer with plenty of water may be permitted.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions For professional users only. Avoid contact with eyes and prolonged skin contact.

Advice on general occupational hygiene Wash contaminated skin thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Keep only in the original container. Keep container tightly sealed when not in use. Store at temperatures between 0°C and 40°C.

Storage class Chemical storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2. Refer to Product Use Guide (PUG) for further information.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Ingredient comments No exposure limits known for ingredient(s).

GREEN PINE DISINFECTANT

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

No specific ventilation requirements.

Eye/face protection

No specific eye protection required during normal use. Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

For users with sensitive skin, it is recommended that suitable protective gloves are worn. Wear protective gloves made of the following material: Nitrile rubber. Rubber (natural, latex).

Hygiene measures

No specific hygiene procedures recommended but good personal hygiene practices should always be observed when working with chemical products.

Respiratory protection

Respiratory protection not required.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Clear liquid.
Colour	Green.
Odour	Pine.
pH	pH (concentrated solution): 9.5-10.5
Initial boiling point and range	100°C
Flash point	Not applicable.
Relative density	~ 1.001 @ 20°C
Solubility(ies)	Soluble in water.
Auto-ignition temperature	Not applicable.
Decomposition Temperature	Not determined.
Viscosity	Non-viscous.
Explosive properties	Not applicable.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

Refractive index	~ 1.8
Volatile organic compound	This product contains a maximum VOC content of <0.1 %.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stability Stable at normal ambient temperatures and when used as recommended.

GREEN PINE DISINFECTANT

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions No potentially hazardous reactions known.

10.4. Conditions to avoid

Conditions to avoid No specific requirements are anticipated under normal conditions of use.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects Information given is based on data of the components and of similar products.

Skin sensitisation

Skin sensitisation May cause sensitisation or allergic reactions in sensitive individuals.

Inhalation

The product is considered to be a low hazard under normal conditions of use.

Ingestion

No harmful effects expected from quantities likely to be ingested by accident.

Skin contact

Skin irritation should not occur when used as recommended. May cause sensitisation or allergic reactions in sensitive individuals.

Eye contact

May cause temporary eye irritation.

SECTION 12: Ecological information

Ecotoxicity The product contains a substance which is harmful to aquatic organisms and which may cause long-term adverse effects in the aquatic environment.

12.1. Toxicity

Toxicity Harmful to Aquatic Organisms

12.2. Persistence and degradability

Persistence and degradability Moderately biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential The product is not bioaccumulating.

12.4. Mobility in soil

Mobility The product is miscible with water and may spread in water systems.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

GREEN PINE DISINFECTANT

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor.
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Discharge of small quantities to the sewer with plenty of water may be permitted.

SECTION 14: Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
----------------	--

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation	<p>Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).</p> <p>Regulation (EU) No 528/2012 of the European Parliament and of the Council of 22 May 2012 concerning the making available on the market and use of biocidal products (as amended).</p> <p>Regulation (EC) No 648/2004 of the European Parliament and of the Council of 31 March 2004 on detergents (as amended).</p> <p>Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).</p> <p>Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work (as amended).</p>
-----------------------	---

GREEN PINE DISINFECTANT

Guidance EH40/2005 Workplace exposure limits
 Containing the list of workplace exposure limits for use with the Control of Substances
 Hazardous to Health Regulations 2002 (as amended)
 Health and Safety Executive

15.2. Chemical safety assessment

A chemical safety assessment has been carried out.

SECTION 16: Other information

Issued by	Regulatory Chemist
Revision date	20/05/2021
Revision	13
Supersedes date	29/03/2021
SDS number	10050
Hazard statements in full	<p>H226 Flammable liquid and vapour. H302 Harmful if swallowed. H314 Causes severe skin burns and eye damage. H315 Causes skin irritation. H317 May cause an allergic skin reaction. H318 Causes serious eye damage. H400 Very toxic to aquatic life. H410 Very toxic to aquatic life with long lasting effects. H412 Harmful to aquatic life with long lasting effects. EUH208 Contains DIPENTENE. May produce an allergic reaction.</p>

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.