




Temperature sensor with process connection

TM-030KFEC01-

/US/



1 1.5" Clamp ISO 2852
L = probe length corresponds to installation length EL



EC 1935/2004 EHEDG Certified FCM FDA

Product characteristics

Measuring range	-40...150 °C	-40...302 °F
Process connection	Clamp DN25...DN40 (1...1,5") DIN 32676 (ISO 2852)	
Installation length EL [mm]	30	

Application

Special feature	Gold-plated contacts	
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)	
Application	hygienic systems	
Media	liquids and gases	
Pressure rating [bar]	25	
Minimum installation depth [mm]	15	
MAWP (for applications according to CRN) [bar]	50	

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Probe length L	[mm]	30	
Measuring range		-40...150 °C	-40...302 °F

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 \times t)$
--------------	-----------------------------------

Response times

Dynamic response T05 / T09 [s]	1 / 3; (to DIN EN 60751)
--------------------------------	--------------------------

Operating conditions

Ambient temperature [°C]	-25...80
Storage temperature [°C]	-40...100
Protection	IP 68; IP 69K



Temperature sensor with process connection

TM-030KFEC01-

/US/

Tests / approvals

Shock resistance	DIN EN 60068-2-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF [years]	22831	

Mechanical data

Weight [g]	181
Materials	stainless steel (1.4404 / 316L)
Materials (wetted parts)	stainless steel (1.4404 / 316L) electropolished
Process connection	Clamp DN25...DN40 (1...1,5") DIN 32676 (ISO 2852)
Surface characteristics Ra/Rz of the wetted parts	Ra: < 0.8
Probe diameter [mm]	6
Installation length EL [mm]	30

Remarks

Remarks	operating voltage "supply class 2" according to cULus The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; Contacts: gold-plated



Connection

