

T50L1STNLM4



Article Number: 111-05423

High Temp Tie, 15.35" Long, 50lb Tensile Strength, PA46, Brown, 1000/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T50L1STNLM4

Type T50L

Color Brown (BN)

- Features and Benefits**
- Cable ties made of PA46 material provide a greater resistance to high heat exposures than PA66 heat stabilized material.
 - Inside serrations allow for strong hold on cables and wire bundles.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description High Temp Tie, 15.35" Long, 50lb Tensile Strength, PA46, Brown, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225.0 N

Length L (Imperial) 15.35 "

Length L (Metric) 390.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.18 "

Width W (Metric) 4.7 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 4.3 "

Bundle Diameter Max. (Metric) 110.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 1000

Carton Quantity 5000

Material and Specifications

Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL94 V2
Operating Temperature	-40°F to +275°F (-40°C to +135°C)
ROHS Compliant	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No