

## Light metal spirit level

**ATORN®**

### Application

For horizontal and vertical alignment of objects



### Version

- Laser-scaled horizontal round vials
- Read off 2% inclines
- Magnifying effect for improved reading
- 270° view of bubble from all positions without any interfering edges
- Made from high-strength non-breakable polycarbonate
- Strong aluminium rectangular profile
- Scratch-proof thanks to special anodising treatment
- Rubber end caps for impact protection

### Advantage

- Silicone pads on rear side surface for non-slip positioning on walls
- Additional divisions for exact 0-position of bubble in the horizontal vial for precise reading (zero-point deviation in normal position: 0.5 mm/m)
- Scale printed on upper measuring surface
- 2 sliding measuring and marking-off tabs

<b>Art. No.</b>	<b>38290 080</b>
<b>Length</b>	800 mm
<b>Measuring accuracy (per length)</b>	0.5 mm/m

### EAN-Code

4050293192100