

**Core drill HSS**  
for universal use up to 1000 N/mm<sup>2</sup>



**Application**

For core drilling pre-drilled, pre-cast or punched holes.

**Version**

- 3-blade design

**Advantage**

- stable grinding combined with the three blades ensure that any mis-alignments and run-out of the pre-made holes are corrected

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	22	20	10	6	4	40	50	40	35	30	25	40		20					

<b>Art. No.</b>	<b>11410 120</b>
<b>Cutting material</b>	HSS
<b>Number of cutting edges</b>	3 PCS
<b>Type</b>	Type N
<b>Cutting edge diameter</b>	12.00 mm
<b>Cutting edge length</b>	134 mm
<b>Length</b>	184 mm
<b>f steel 700</b>	0.08 mm/U
<b>DIN</b>	344

**EAN-Code**

4050293010510